L legrand[®]

Bticino S.p.A. Viale Borri, 231 – 21100 Varese (VA) – ITALY www.bticino.com – www.legrand.com

TAZ 90° elbows

Item codes : from 386391 to 386396 and 386398

SUMMARY

PAGES

- 1. Description and applications1
- 2. Dimensions and compatibility1
- 3. Technical features1


5. Conformity and approvals.....2

1. DESCRIPTION AND APPLICATIONS

Galvanized steel elbows (electrical welded with zinc deposited on welding). Suitable for static applications where are required very high mechanical and thermal performances. it has a good resistance to chemicals and corrosion and guarantee an IP68 protection when used with TILOK connectors. It's the ideal solution for energy, signal or power distribution in industrial, commercial, infrastructures and residential applications.

2. DIMENSIONS AND COMPATIBILITY


Dimensions and packaging:



| Item | External diameter [mm] | S [mm] | L [mm] | C [mm] | Pack [pcs] |
|--------|------------------------------|-----------|-----------|-----------|---------------|
| 386391 | 16 | 1,0 | 123,0 | 70,0 | 100 |
| 386392 | 20 | 1,0 | 137,0 | 77,0 | 50 |
| 386393 | 25 | 1,2 | 168,0 | 86,0 | 100 |
| 386394 | 32 | 1,2 | 202,0 | 86,0 | 50 |
| 386395 | 40 | 1,2 | 226,0 | 86,0 | 25 |
| 386396 | 50 | 1,2 | 299,0 | 124,0 | 10 |
| 386398 | 63 | 1,5 | 351,0 | 150,0 | 5 |

Compatibility:

Connectors, fittings and accessories TILOK series, SILOK series, MECHANICAL series, metal accessories and equipments.



Technical data sheet: IDP000085EN/01

Updated: 25th November 2014

Created: 25th November 2014

TAZ 90° elbows


Resistance to chemical agents:

Represents the resistance to chemicals or external agents. The used test method consist of: immersion of the items under test in the chemical substance for 24 hours; once they were dried and conditioned at a constant temperature for other 24 hours, they were checked with the following examinations:

- Visual inspection to check the integrity
- Mechanical bending test
- Mechanical compression test
- IP protection test

| Industrial chemical agents | Resistance* |
|----------------------------|-------------|
| Unleaded petrol | • |
| Industrial detergent | |
| Diesel fuel | |
| Lubricant oil | |
| Emulsifier solution | • |
| Washing solvent | • |

* resistances to chemicals are indicative. For any specific application or environment please contact Legrand technical offices



- Medium resistance
- No resistance

Operating temperature:


Minimum: -25° C / -13° F Maximum: +150° C / +302° F

Electric properties:

Electric continuity guaranteed

IP protection index:

IP68 with TILOK series connectors. IP65 with MECHANICAL series connectors.



| 2 nd digit IP | | | | |
|--|--|--|--|--|
| Protection against the ingress of liquids | | | | |
| C. | Protection against drops of water falling at up to 15° from the vertical | | | |
| * | 3 Protection against drops of rain water at up to 60° from the vertical | | | |
| 0 | 4 Protection against sprays of water from all directions | | | |
| | 5 Protection against jets of water from all directions | | | |
| | 6 Protection against jets of water of similar force to heavy seas | | | |
| | 7 Protection against the effects of immersion | | | |
| e] O | 8 Protection against prolonged effects of immersion under pressure | | | |

For technical documentation, test reports, commercial information or any other needs please refer to the local LEGRAND office.

Technical data sheet: IDP000085EN/01

Updated: 25th November 2014

4. ENVIRONMENTAL PROFILE

All the items identified in this technical sheet respect in terms of concentration of substances and raw materials the European legislations about dangerous and forbidden substances and chemical preparations.

5. CONFORMITY AND APPROVALS

CE

All the items identified in this technical sheet are compliant to all the requirements and the regulations currently in force in the European Union about safety, health and environmental issues.



IMQ mark: items from 386391 to 386396 and 386398.