




	RJ 45 (PoE/PoE+ class 0) or • Screw terminal block (27_50 V±/V=)
	RJ 45 IP Network
$X =$	$X = 12$
	-5°C → +45°C
	NF EN50428 IEC 60669-2-1





Power supply



27-50 V~/= **or** PoE/PoE+
6 W








D	Ø
≤ 100 m	0,5 mm ²
≤ 150 m	0,75 mm ²
≤ 300 m	1,5 mm ²



A - B	230 V~											250 VA	1,1 A	250 VA	1,1 A				
	110 V~											125 VA		125 VA					
	12 - 48 V~ /V=											13-52 VA	1,1 A	13-52 VA	1,1 A				
C - D	230 V~	160 VA	0,7 A	500 VA	2,1 A	500 VA	2,1 A	4 (2 x 36) W	1,7 A	160 VA	0,7 A	160 VA	0,7 A	1000 W	4,3 A	500 VA	2,1 A	500 VA	2,1 A
	110 V~	80 VA		250 VA		250 VA		2 (2 x 36) W		80 VA		80 VA		500 W		250 VA		250 VA	
E - F	230 V~	500 VA	2,1 A	1000 VA	4,3 A	1000 VA	4,3 A	10 (2 x 36) W	4,3 A	500 VA	2,1 A	500 VA	2,1 A	3680 W	16 A	500 VA	2,1 A	500 VA	2,1 A
	110 V~	250 VA		500 VA		500 VA		5 (2 x 36) W		250 VA		250 VA		1760 W		250 VA		250 VA	







→
OK

Input	G1	G2	G3	G4	G5	G6	G7	G8
Output	A1	A2	B1	B2	C1	C2	C3	C4
Action	UP/ STOP	DOWN/ STOP	UP/ STOP	DOWN/ STOP	ON/ OFF	ON/ OFF	ON/ OFF	ON/ OFF

Input	H1	H2	H3	H4	H5	H6	H7	H8
Output	D1	D2	D3	D4	E1	E2	F1	F2
Action	ON/ OFF	ON/ OFF	ON/ OFF	ON/ OFF	ON/ OFF	ON/ OFF	ON/ OFF	ON/ OFF

USB
Reset
RJ 45