


LIVING-LIGHT

Wake Up / Sleep wireless switch



Use

It is equipped with 2 buttons for activating Wake up / Sleep scenarios.

Scenarios can be customized by the Home + Control app.

Surface installation with repositionable stickers (supplied) or onto a flush mounting box. Integrated LED for low battery indication.

Powered by battery 3V type CR2032 (supplied) with an autonomy of 8 years - 2 modules.

Standards and approvals

The under signed, BTICINO, declares that the radio-electric equipment type (N-NT-L4574CW) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: www.bticino.it/red

Range Designation Cat. Nos. Wake up / Sleep wireless control, with battery. □ N4574CW Equipped with an LED indicator (confi-guration) and a RESET button (hidden) used to return to factory settings. NT4574CW Repositionable self-adhesive fixings supplied. L4574CW


Colours code:

 \square White

Silver

Anthracite

Dimensions (mm)



A	В	C
74	74	11

Technical characteristics

- Mechanical characteristics

Protection against impacts: IK 02

Protection against solid bodies/liquids: $\;$ IP 20 without plate and rocker plate

- Material characteristics

Mechanism with grid: Fibreglass-reinforced (10%) PC

Mechanism functional cover: PC/ABS

Supporting base: fiberglass-reinforced PA (60%).

Halogen-free UV resistant

Self-extinguishing: 650°C/30 s

- Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)

Battery life: 8 years for 10 activations a day **ZigBee radio technology** frequency: 2.4 GHz to 2.4835 GHz

Wireless mesh network, self-adaptive and secure (AES 128), conforming to standard

IEEE 802.15.4 (LR-WPAN)

Power level: < 100 mW

- Climate characteristics

Usage temperature: $+5^{\circ}$ C to $+45^{\circ}$ C Storage temperature: 0° C to $+45^{\circ}$







Wake Up / Sleep wireless switch

Operation

Front view



Front view without coverkey



Legend

- 1. Control pushbutton
- 2. LED indicator: useful during installation
- 3. RESET button used to return to factory settings

Care

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

${\bf Caution: Always\ test\ before\ using\ special\ cleaning\ products.}$

The plates must not be painted.



Take care to recycle the battery appropriately.

RAEE/WEEE: bticino.com/disposal

