














9) 7:2? = 1): " = ?0: '@\*' ) (: '\*') : '2', A/7B'''  
 C"! '\*?' '3'1): 2B17"D"E/7>"F\*) 1(: "G"


F\*H171<      ¶<<  
 <<<<      ¶<  
 J \*HQ01k. % - / \$ E C<

\< FNJ J YR9F - &9NR

+ (AB = /"H1" \_2/) (A1 = 1): "O + M[V"J \*H\_??"




+ (AB = /"H1" \_2/) (A1 = 1): "O + M[V"J \*H\_??" / b1 ("J ')" "v 1\_ + 12b1??"



a1 c O + M[V"Y: "07/: '\*') , 217(2: 1"H1"(g\_01"%10H1)"\[M35"%10H1)"4! 6T - "a\*?"BZ?'b/01):c, \*???)1"0\*)X?1??" = /d'=?="H?"\_?"H1"! 666" = "\*"?"H1  
 (g\_01"H1"F/:BX\*2'1"T"aK&W"\*?"Y&Wc", \*???)1"0\*)X?1??" = /d'=?="H1"V6" = <  
 a3c OB7'7:/) (1"H1":12=) /'7\*) "H1"! 36" ") :BX2B1"C0") 7:2? = 1):  
 a4c E:A12)1:"F/:<"T"aK&W#Y&Wc  
 a4c ]/\_\*\_2)1"D"+S"G")1"H\*":, /7'm:21"\_2/) (AB1"C0"/:1221<

+ (AB = /"H1" \_2/) (A1 = 1): "J \_??"



Connexions non polarisées  
 (5) Un câble téléphonique standard à deux Is (JYST N°2\*0.8 mm)

&/\_01/?d"H1"(\* == ?) ('/: '\*') "

8 ]17", 2\*: (\*017"H1"(\* == ?) ('/: '\*') "J NL%Y + "1:"J %Y + "\*" ): "H7, \*) \_017"7??01"7:1"UUU0TXXXJ NFTZTGS

9) @\* , 2\*H?: ! "9LW6664M[KOK6! "

J \*H@B1"011"8"

W21 = 'Q21"b127'\*) ! " \#63#363! "

