



LIVING

now

### Cat. No(s): K4001A - K4003A - K4005A K4001M2A - K4003M2A - K4005M2A

# Basic control devices - 1-way - 2-way - momentary switch





## 1. USE

Axial switch control device for lighting and other control.

#### 2. RANGE


Designation	Cat. No.	Related Cover Code
1-way switch 10 AX - 250 V	K4001A	KW01- KW01A - KW01D - KW01F - KW01X
	K4001M2A	KW01M2-KW01M2A- KW01M2D - KW01M2F - KW01M2X
2-way switch 10 AX - 250 V	K4003A	KM01 KM01A - KM01D KM01F - KM01X
	K4003M2A	KM01M2 - KM01M2A - KM01M2D - KM01M2F - KM01M2X
Momentary 1P switch 10 A - 250 V	K4005A	KG01 - KG01A - KG01D KG01F - KG01X -
	K4005M2A	KG01M2 - KG01M2A - KG01M2D - KG01M2F - KG01M2X


Colours code:


□ White


Sand Black

# 3. OVERALL DIMENSIONS (mm)









#### **4. CONNECTION**

Automatic clamps for all devices. Stripping length (rigid or flexible cables): 12 mm

#### **5. TECHNICAL CHARASTERISTICS**

#### 5.1 Protection index

Penetration by solid bodies/liquid: IP 21 D Impact test: IK 04

#### **5.2** Material characteristics

Material: Polycarbonate for mechanism case Halogen free. UV resistant. Self-extinguishing: - 850° C / 30 s for insulating parts holding live parts in place. - 650° C / 30 s for other parts made of insulating materials.

#### ■ 5.3 Electrical characteristics

Voltage: 250 VAC Current: 10AX

#### **5.4 Climatic charasteristics:**

Storage and operating temperatures: - 5° C to + 35° C

## 6. CLEANING

Surface cleaning with a cloth. Do not use: acetone, tar remover, trichloroethylene.

Caution: A preliminary test should be carried out if other specific cleaning products are to be used. ······

#### 7. STANDARDS AND APPROVALS

Compliance with standards of installation and manufactoring. Refer to e.catalogue.