





# RD2E2



# RD2G2



## DESCRIZIONE FRONTALE

- 1 Predisposizione IΔn soglia d'intervento
- 2 Selettore portata x1 / x10 / x100

IΔn

	0,05	0,075	0,1	0,15	0,2	0,3
x1	50mA	75mA	100mA	150mA	200mA	300mA
x10	500mA	750mA	1A	1,5A	2A	3A
x100	5A	7,5A	10A	15A	20A	30A

Controllare che il valore d'intervento selezionato sia compatibile con le sensibilità minima rilevabile dal trasformatore toroidale abbinato.

- 3 • 4 LED segnalazione

3 On	4 Trip / Fail	
•	•	Assenza tensione alimentazione ausiliaria o apparecchio fuori servizio Lack of auxiliary voltage supply or out of order meter
••	•	Sorveglianza • Supervision
•••	••	Allarme • Alarm
••••	••••	Interruzione collegamento toroide - relè Connection breakdown between relay and ring current transformer

LED spento  
LED acceso  
LED lampeggiante

## FRONT DESCRIPTION

- 1 Setting intervention threshold IΔn
- 2 Range selector x1 / x10 / x100

- 3 • 4 Signaling LED

- 5 Pulsante di prova
- 6 Reset key

It allows to simulate alarm condition, LED Trip switching on and output relay switching.  
Reset is not possible with persistent residual current: > 50% IΔn.

- 7 Selector AL.2 / AL.50%

AL.2 = alarm relay with double SPDT exchange.  
AL.50% = alarm relay + pre-alarm relay. Relay marked 60 - 61 - 62 is a pre-alarm state with fixed intervention threshold, equal to 50% of selected IΔn value.

- 8 Switch for state of output relay: Nd (normally de-energised) negative security, Ne (normally energised) positive security.

Pre-alarm relay is always normally de-energized.

- 9 Setting intervention delay

Instantaneous display of earth leakage current (in % of selected IΔn value)

On-off harmonic filter

- 5 Pulsante di prova

Permette di simulare la condizione di allarme, l'accensione del LED Trip e la commutazione del relè d'uscita.

- 6 Pulsante di ripristino

Il ripristino è inibito con corrente differenziale persistente: > 50% IΔn impostata.

- 7 Selettore AL.2 / AL.50%

AL.2 = relè di allarme con doppio scambio SPDT.  
AL.50% = relè di allarme + relè di preallarme. Il relè contrassegno 60 - 61 - 62 è un preallarme con soglia intervento fissa, pari al 50% del valore di IΔn selezionato.

- 8 Selettore stato relè uscita: Nd (norm. diseccitato) sicurezza negativa - Ne (norm. eccitato) sicurezza positiva.

Il relè di preallarme è sempre norm. diseccitato.

- 9 Predisposizione ritardo intervento

Indicazione istantanea della corrente differenziale (in % del valore IΔn impostato)

Inserzione (on) - esclusione (off) filtro per componenti armoniche.

### ISTRUZIONI DI CABLAGGIO

- Applicazioni industriali onerose, con presenza di correnti distorte: inverter, variatori di velocità, carichi non lineari.  
**Non utilizzabile per la protezione delle persone.**
- La posizione di fissaggio risulta completamente indifferente ai fini del funzionamento.
- **Le operazioni di predisposizione (soglia intervento, tempo ritardo, ecc.) devono essere effettuate con apparecchio non alimentato.**
- Rispettare scrupolosamente lo schema d'inserzione, una inesattezza nei collegamenti è inevitabilmente causa di funzionamento anomalo o di danni all'apparecchio.
- L'ottenimento della piena funzionalità del sistema di protezione differenziale è legato alle modalità di installazione, per cui si consiglia:
  - ☞ Ridurre al minimo la distanza tra toroide e relè
  - ☞ Utilizzare cavi schermati o intrecciati per la loro connessione
  - ☞ Evitare di disporre i cavetti di connessione toroide-relè parallelamente a conduttori di potenza
  - ☞ Evitare di installare toroide e relè in prossimità di sorgenti di campi elettromagnetici intensi (grossi trasformatori).
  - ☞ Solo i conduttori attivi attraversano il toroide (dis.D1)
  - ☞ Utilizzando cavo schermato, l'armatura deve essere collegata a terra come da (dis.D2)
  - ☞ I conduttori devono essere posizionati al centro del toroide (dis.D3).

### WIRING INSTRUCTIONS

- Heavy industrial applications with distorted current waveforms: inverters, variable speed drives, rectifiers, frequency regulators.  
**It cannot be used to protect people**
- Mounting position do not affect in any way the proper working.
- **Setting operations (intervention threshold, delay time, etc.) must be carried out with non-fed meter.**
- Please carefully follow the wiring diagram; an error in connecting the relay may give rise to irregular working or damages.
- Four full functional of the earth relay the following installation recommendation should be adopted.
  - ☞ To reduce as much as possible the distance between ring current transformer and relay.
  - ☞ To use only shielded or twisted cables for their connection
  - ☞ To avoid in placing ring current transformer-relay connection cables parallelly to power wires
  - ☞ To avoid in mounting ring current transformer and relay near sources of intense electromagnetic fields (big transformers).
  - ☞ Pass active conductor only through toroid (draw D1)
  - ☞ When using blind cable, ensure ground connection of armature (draw D2)
  - ☞ Ensure the central positioning of conductor through toroid (draw D3).

## Istruzioni d'uso User's Guide

LE12565AA 10/20 - 01 IM




A Group brand | Legrand

BTicino SpA  
Viale Borri, 231  
21100 Varese - ITALY




www.imeitaly.com


**DIMENSIONE DI INGOMBRO • OVERALL DIMENSIONS**




**D1**



**D2**



**D3**



NUCLEO CHIUSO / CLOSED CORE					NUCLEO APRIBILE / OPEN CORE				
CODICE CODE	PASSAGGIO CAVO PASSING CABLE	$I_{\Delta n}$ min <sup>(1)</sup> A	$I_n$ A	$I_{max}$ <sup>(2)</sup> A	CODICE CODE	PASSAGGIO CAVO PASSING CABLE	$I_{\Delta n}$ min <sup>(1)</sup> A	$I_n$ A	$I_{max}$ <sup>(2)</sup> A
<b>TDGA2</b>	<b>Ø 28</b>	<b>0,03</b>	<b>65</b>	<b>390</b>	<b>TDAA2</b>	<b>Ø 110</b>	<b>0,5</b>	<b>250</b>	<b>1500</b>
<b>TDGB2</b>	<b>Ø 35</b>	<b>0,03</b>	<b>70</b>	<b>420</b>	<b>TDAB2</b>	<b>Ø 150</b>	<b>0,5</b>	<b>250</b>	<b>1500</b>
<b>TDGH2</b>	<b>Ø 60</b>	<b>0,03</b>	<b>90</b>	<b>540</b>	<b>TDAC2</b>	<b>Ø 300</b>	<b>1</b>	<b>630</b>	<b>3780</b>
<b>TDGC2</b>	<b>Ø 80</b>	<b>0,05</b>	<b>170</b>	<b>1020</b>					
<b>TDGD2</b>	<b>Ø 110</b>	<b>0,1</b>	<b>250</b>	<b>1500</b>					
<b>TDGE2</b>	<b>Ø 140</b>	<b>0,3</b>	<b>250</b>	<b>1500</b>					
<b>TDGF2</b>	<b>Ø 210</b>	<b>0,3</b>	<b>400</b>	<b>2400</b>					





<sup>(1)</sup> Minima corrente  $I_{\Delta n}$  valore minimo di  $I_{\Delta n}$  impostabile sul relè differenziale abbinato al toroide  
 $I_{\Delta n}$  lowest current  $I_{\Delta n}$  lowest value that can be set on earth leakage relay connected with toroid

<sup>(2)</sup> Corrente di test corrispondente a  $6I_n$ :  $I_{max}$  (IEC/EN 60947-2 annex M)  
 Test current corresponding to  $6I_n$ :  $I_{max}$  (IEC/EN 60947-2 annex M)

**SICUREZZA NEGATIVA • NEGATIVE SECURITY**

**AL.2**

**SICUREZZA POSITIVA • POSITIVE SECURITY**



**SICUREZZA NEGATIVA • NEGATIVE SECURITY**

**AI.50%**

**SICUREZZA POSITIVA • POSITIVE SECURITY**

