



LIGHT now

- One-way switches
- Two-way switches
- Pushbuttons


Y4001A - Y4003A - Y4005A
 YW4001A - YG4001A- YD4001A
 YW4003A - YG4003A - YD4003A
 YW4005A - YG4005A - YD4005A
 YW40034A - YG40034A - YD40034A
 YW4001M2A - YG4001M2A- YD4001M2A
 YW4003M2A - YG4003M2A - YD4003M2A
 YW4005M2A - YG4005M2A - YD4005M2A



Y4001A - Y4003A - Y4005A



..4001A - ..4003A - ..4005A - ..4034A



..4001M2A - ..4003M2A - ..4005M2A

Use

Rocker control device for lighting and other loads.


Range

Designation	Item
One-way 1P 10AX - 250Va.c. lightable with led lamp (see table below)	☐ YW4001A - YW4001M2A ☐ YG4001A - YG4001M2A ☐ YD4001A - YD4001M2A ☒ Y4001A
Two-way 1P 10AX - 250Va.c. lightable with led lamp (see table below)	☐ YW4003A - YW4003M2A ☐ YG4003A - YG4003M2A ☐ YD4003A - YD4003M2A ☒ Y4003A
Pushbutton 1P 10AX - 250Va.c. lightable with led lamp (see table below)	☐ YW4005A - YW4005M2A ☐ YG4005A - YG4005M2A ☐ YD4005A - YD4005M2A ☒ Y4005A
Opening Pushbutton 1P (NO - NC)10A - 250Va.c. lightable with led lamp (see table below)	☐ YW4034A ☐ YG4034A ☒ YD4034A

LED Color	230 Va.c.	12/24 Va.c.
White	LN4742V230T	LN4742V12T
Blue	LN4742V230B	

Colors: ☐ White ☐ Stone ☐ Black

Overall dimensions (mm)



	A	B	C	D
..4001A / ..4003A / ..4005A / ..4034A	45.1	22.3	38.1	11.9
..4001M2A / ..4003M2A / ..4005M2A	45.1	44.7	38.1	11.9

Connection

Terminal type: automatic clamp
 Terminal capacity: 2 x 4 mm² max
 Stripping length: 12 mm
 Compatible with flexible or rigid cables

Technical characteristics

- **Protection index:**
 (considering a complete installation, including cover plate)
 - Penetration by solid bodies/liquid: IP40
 - Impact test: IK04
 - **Material characteristics:**
 - Case: PC (polycarbonate)
 - Key cover : ABS
 - Halogen Free
 - UV resistant
 - Self-extinguishing:
- 850°C/30s for insulating parts holding live parts in place.
 650°C/30s for other parts made of insulating material.

Electrical characteristics:

- Voltage: 250 V a.c.
- Current: 10AX

Climatic characteristics:

- Storage temperature : -10° C a +70° C
- Use temperature: -5° C a +35° C

Cleaning

Clean the surface with a cloth.
 Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

Standards and approvals

Compliance with standards IEC/EN 60669-1.
 Refer to e.catalogue.