




Socket outlets - Italian Standard



..4113.



..4180.



..4140A16F

Use

Socket outlets for: Italian standard, Italian and German standard plugs.

Range

Designation

Item

Socket 2P+T 10A 250Va.c. - centre distance 19 mm
 shielded tulip contacts Ø4 mm
 for plug 2Pe2P+T10A Italian standard
 1 module

- | | |
|---------------------------------|---------------------------------|
| <input type="checkbox"/> YW4113 | <input type="checkbox"/> Y4113R |
| <input type="checkbox"/> YG4113 | <input type="checkbox"/> Y4113O |
| <input type="checkbox"/> YD4113 | <input type="checkbox"/> Y4113G |

Socket 2P+T 10A and 16A 250Va.c.
 centre distance 19/26 mm - shielded tulip contacts
 for plug 2Pe2P+T 10A and 16A Italian standard
 1 module

- | | |
|---------------------------------|---------------------------------|
| <input type="checkbox"/> YW4180 | <input type="checkbox"/> Y4180R |
| <input type="checkbox"/> YG4180 | <input type="checkbox"/> Y4180O |
| <input type="checkbox"/> YD4180 | <input type="checkbox"/> Y4180G |


Socket FLAT 2P+T 10A and 16A 250Va.c.
 centre distance 19/26 mm - shielded tulip contacts
 earth side contacts for German standard plugs
 suitable for Italian standard plugs 2P and 2P+E 10/16A,
 German standard plugs 2P+E 16A
 2 modules

- | | |
|-------------------------------------|-------------------------------------|
| <input type="checkbox"/> YW4140A16F | <input type="checkbox"/> Y4140A16FR |
| <input type="checkbox"/> YG4140A16F | <input type="checkbox"/> Y4140A16FO |
| <input type="checkbox"/> YD4140A16F | <input type="checkbox"/> Y4140A16FG |

Colors:

- White Stone Dark Red Orange Green

Overall dimensions (mm)



	A	B	C	D
1 module ..4113 / ..4180	45.1	22.3	37.5	8.6
2 modules ..4140....	45.1	44.7	41.5	8.6

Connection

Terminal type: screw clamp
 Terminal capacity: 2 x 4 mm² max
 Stripping length: 11 mm
 Compatible with flexible or rigid cables

Technical characteristics

- **Protection index:**
 (considering a complete installation, including cover plate)
 - Penetration by solid bodies/liquid: IP21D
 - Impact test: IK04
- **Material characteristics:**
 - Case: PC (polycarbonate)
 - Key cover: PC (polycarbonate)
 - Halogen Free
 - UV resistant
 - Self-extinguishing:
 - 850°C/30s for insulating parts holding live parts in place.
 - 650°C/30s for other parts made of insulating material.
- **Electrical characteristics:**
 - Voltage: 250 V a.c.
 - Current: 10A or 16A
- **Climatic characteristics:**
 - Storage temperature: -10° C a +70° C
 - Use temperature: -5° C a +35° C

Cleaning

Clean the surface with a cloth.
 Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

Standards and approvals

Compliance with standards CEI 23-50 / IEC60884-1
 Refer to e.catalogue.