



0 580 18/19





	0 580 18	0 580 19
P	7.4 kW - 22 kW	
U	230 V - 400 V	
A	32 A	
IP	55	
IK	10	
🌡️	- 25°C / + 55°C	
Communication	RS485 - Ethernet - 4G	
RFID (desactivable)	Oui/Yes	


0 590 53







0 590 54




0 590 53













1




2




3




4






0 590 54


1



2



3



5



Lina 12.5 0 360 22
Lina 25 0 360 16

0 360 56

M8

0 361 53 + 0 367 81

M8











0 580 18

Ph+N

3P+N





				Legrand France		Legrand International		Bticino	
0 580 18	A	kW	Ø min. (mm²)	KM1	Q1	KM1	Q1	KM1	Q1
Ph + N	16	3,7	2.5	4 062 76	4 107 54	4 062 76	4 110 95	F80ST1	GN8813F16
	20	4,6	4		4 107 55		4 110 96		GN8813F20
	25	5,8	6		4 107 56		4 110 97		GN8813F25
	32	7,4	10		4 108 59		4 110 98		GN8813F32
3P + N	16	11	2.5	4 062 76	4 112 45	4 062 76	4 112 45	F80ST1	GN8843F16
	20	15	4		4 112 46		4 112 46		GN8843F20
	25	18	6		4 112 47		4 112 47		GN8843F25
	32	22	10		4 079 02 + 4 105 33		4 079 32 + 4 105 34		GN8843F32

Pour la section de câble à utiliser : se référer aux notes de calculs / For the cable section to use: refer to the calculation notes





0 580 19

Ph+N







3P+N



				Legrand France		Legrand International		Bticino	
0 580 19	A	kW	Ø min. (mm²)	KM1 x 2	Q1 x 2	KM1 x 2	Q1 x 2	KM1 x 2	Q1 x 2
Ph + N	16	3,7	2.5	4 062 76	4 107 54	4 062 76	4 110 95	F80ST1	GN8813F16
	20	4,6	4		4 107 55		4 110 96		GN8813F20
	25	5,8	6		4 107 56		4 110 97		GN8813F25
	32	7,4	10		4 108 59		4 110 98		GN8813F32
3P + N	16	11	2.5	4 062 76	4 112 45	4 062 76	4 112 45	F80ST1	GN8843F16
	20	15	4		4 112 46		4 112 46		GN8843F20
	25	18	6		4 112 47		4 112 47		GN8843F25
	32	22	10		4 079 02 + 4 105 33		4 079 32 + 4 105 34		GN8843F32

Pour la section de câble à utiliser : se référer aux notes de calculs / For the cable section to use: refer to the calculation notes



Caractéristiques techniques⁽¹⁾ / Technical characteristics⁽¹⁾

Installation / Installation

Intérieur ou extérieur, zone d'accès non limitée (hors voirie), destinée à être utilisée par des personnes ordinaires (DBO), ensemble en coffret (fixation murale) ou en armoire (fixation au sol), degré de pollution 3 à l'extérieur du produit (pollution 2 à l'intérieur du produit), régime de neutre compatible TNS, TT.

En cas de régime de neutre en IT, il est possible de changer localement le régime de neutre par l'ajout d'un transformateur d'isolement. Construction fixe.

Interior or exterior, unlimited access zone (excluding roads), intended for use by ordinary persons (DBO) assembly in cabinet (wall mounted) or enclosure (floor mounted),

Pollution Degree 3, TNS, TT, compatible earthing system.

In the event of an IT earthing system, this can be changed locally by adding an isolating transformer. Fixed construction

Environnement / Environment

Température d'utilisation / Operating temperature	-25°C / +55°C
Température de stockage / Storage temperature	-25°C / +70°C
Classe de corrosivité / Corrosivity class	C4 élevée 720h selon ISO 9227 - C4 élevée selon ISO 9223 4C high 720h according to ISO 9227 - 4C high according to ISO 9223
Indice de protection / Protection rating	IP 55 (IEC 60529), medium resistance (IEC 61439-7) + IK 10 (EN 62262)
Exposition solaire / Exposure to sunlight	Test ISO 4892-2 Weatherometer 1250h Méthode A / ISO 4892-2 Weatherometer test, 500 hrs Method A

