




- Four-way axial switches




Y4054..



Y4054M2..



Y..4054



Y..4054M2

Use


Axial control device for lighting and other loads, 1M and 2M.

Range

Designation	Item
Four-way axial 1P 10AX - 250Va.c. not lightable	☐ YW4054 - YW4054M2 ☐ YG4054 - YG4054M2 ☒ YD4054 - YD4054M2 ☒ Y4054 ☒ Y4054M2
Four-way axial 1P 10AX - 250Va.c. Supplied with white LED for backlighting (the LED is not interchangeable)	☒ Y4054LW ☒ Y4054M2LW
Four-way axial 1P 10AX - 250Va.c. Supplied with blue LED for backlighting (the LED is not interchangeable)	☒ Y4054LB ☒ Y4054M2LB

Colors: ☐ White ☒ Stone ☒ Dark

Overall dimensions (mm)



	A	B	C	D
..4054	45.1	22.3	38.2	8.6
..4054M2	45.1	44.7	38.2	8.6

Connection

Terminal type: screw clamp
Terminal capacity: 2 x 4 mm² max
Stripping length: 9 mm
Compatible with flexible or rigid cables

Technical characteristics

- **Protection index:**
(considering a complete installation, including cover plate)
 - Penetration by solid bodies/liquid: IP40
 - Impact test: IK04
 - **Material characteristics:**
 - Case: PC (polycarbonate)
 - Key cover: ABS
 - Halogen Free
 - UV resistant
 - Self-extinguishing:
- 850°C/30s for insulating parts holding live parts in place.
650°C/30s for other parts made of insulating material.
- **Electrical characteristics:**
 - Voltage: 250 V a.c.
 - Current: 10AX for ..4054..
 - **Climatic characteristics:**
 - Storage temperature: -10° C a +70° C
 - Use temperature: -5° C a +35° C

Cleaning

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

Standards and approvals

Compliance with standards IEC/EN 60669-1.

Refer to e.catalogue.