


USB Type-C charger - 45 W



1. USAGE

Allows you to power and charge multimedia terminals: PC, tablets, smartphones.

USB Power Delivery and Quick charge are new fast charging technologies built into iOS/Apple and Android/Google devices.


Technologies enabling a faster charging level than conventional technologies, operating via an exchange between the terminal and the charger.

2. RANGE

Designation	Item
1 USB Type-C 45W (1 output Type-C)	<input type="checkbox"/> YW4294C
2 modules	<input type="checkbox"/> YG4294C
	<input type="checkbox"/> YD4294C

Colors: White Stone Dark

3. DIMENSIONS (mm)



A	B	C	D
45	45	45	8.6

4. CONNECTION

Type of terminals: with screws

Terminal capacity: 2 x 2.5 mm²

Stripping length: 6 mm

Screwdriver: flat 3.5 mm

Circuit breaker: 16 A MAX.

Necessary safety precautions:



Switch OFF the power at the main circuit breaker. Make sure that the power is OFF before continuing with the installation.

5. TECHNICAL CHARACTERISTICS

5.1 Mechanical characteristics

Impact tests: IK 04

Penetration by solid bodies and liquids: IP 40

5.2 Material characteristics

Mechanism casing: PA 6.6 V-0 UL

Cover: ABS

Halogen-free

UV-resistant

Self-extinguishing:

PA 6.6 V-0 UL

650°C/30 s for other insulating components.

5.3 Climate characteristics

Storage temperature: -20°C to +70°C

Operating temperature: +5°C to +40°C

USB Type-C charger - 45 W

5. TECHNICAL CHARACTERISTICS *(continued)*

■ 5.4 Electrical characteristics

All values listed below are measured at an ambient temperature of + 20° and after 30 minutes of operation.

Nominal input voltage	220-240V~
Nominal input frequency	50/60Hz
Max. output power	45,0W
Nominal input current	0.8A
Max. nominal output current	3.0A
Average efficiency in active mode	88%
Nominal output voltage	5.0V [≡] *
Stand-by power consumption	0.08W
Consumption class without load and average level of efficiency: Level VI	
Protection class	II - Low voltage

*Optimise/voltage:

5.0V [≡]	3.0A
9.0V [≡]	3.0A
12.0V [≡]	3.0A
15.0V [≡]	3.0A
20.0V [≡]	2.2A

Note: To optimize the charging time of your device, ensure turn it off during the charging phase.

6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistance to the following agents:

Hexane (EN 60669-1), methylated spirits, soapy water, diluted ammonia, pure bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using other special cleaning products

7. STANDARDS AND APPROVALS

Compliant with installation and manufacturing standards.

See e.catalogue.