MODBUS TABLE ORGANIZATION

Starting Address of the Group	tarting Address of the Group Starting Address of the Group		System Version	Group Name (Text)	Group Code	Group Complexity	Group Version
Registers (Dec)	Registers (Hex)	(Release)	(Build)		(Hex)	(Hex)	(Hex)
16384	4000	01	11	State of Breaker	51 02	10	01 00
29184	7200	01	11	Three-phase Electric Protection	73 03	20	01 00
20480	5000	01	11	Three-phase Electric Measurement	71 03	30	01 00
32768	8000	01	11	Single-channel Thermal Measurement	81 00	10	01 00

MODBUS PROTOCOL DETAILS

Function Code (Dec)	Exception Codes (Dec)	Data Encoding
2 (Read Discrete Inputs)	1, 2, 3	"Big Endian" (most
		significant byte first)
4 (Read Input Registers)	1, 2, 3	"Big Endian" (most
		significant byte first)

MODBUS OVER SERIAL DETAILS

Physical Layer	Trasmission Modes	Device Addressing	Baud Rates (bit/s)	Data Bits	Data bits trasmission	Parity	Stop Bits
standard EIA/TIA 485 (RS-485) two- wire configuration	RTU	1÷247	programmable (1200, 2400, 4800, 9600, 19200, 38400)		Least significant bit first	NONE	1

MASTER/SLAVE COMMUNICATION TIMING

Timer Description	Timer Value (msec)
Inter-character time-out	< 1,5 character times
Response delay (from master request)	-
Delay Time (between two master trasmissions)	-

www.modbus.org - MODBUS over serial line specification and implementation guide V1.02 - MODBUS APPLICATION PROTOCOL SPECIFICATION V1.1b REFER ALSO TO:

NOTE: File and printed copies of this document are not subject to document change control.

Register Number	Register Address (Dec)	Register Address (Hex)	Dimension [bit]	Description	Note	Read Function Codes	Data Storing
16385	16384	4000	3	State of Breaker			
16385	16384	4000	1	Open	The information reported here "self-resets" when the condition that generated it ends.	2	
16386	16385	4001	1	Closed	The information reported here "self-resets" when the condition that generated it ends.	2	
16387	16386	4002		Tripped	The information reported here "self-resets" when the condition that generated it ends.	2	
29185	29184	7200	14	Three-phase Electric Protection			
29185	29184	7200	1	Overload pre-alarm (threshold I1)	The information reported here "self-resets" when the condition that generated it ends.	2	
29186	29185	7201	1	Overload alarm (>threshold I2)	The information reported here "self-resets" when the condition that generated it ends.	2	
29187	29186	7202	2	RESERVED (returns "0")			
29189	29188	7204	1	Over-temperature alarm (>threshold T)	The information reported here "self-resets" when the condition that generated it ends.	2	
29190	29189	7205	4	RESERVED (returns "0")			
29194	29193	7209	1	Overload P. Relay Tripped (no phase indication)	The information reported here is maintained even when the condition that generated it ends. The "restore" conditions can be (equivalent, in alternative): • the detection of the device in Closed state • the detection of a minimum current value on the phases. The presence of Switch State Functionality is therefore NOT binding (Example: if the switch goes back to Open => the	2	Y
29195	29194	720A	1	Short circuit P. Relay Tripped (no phase indication)	The information reported here is maintained even when the condition that generated it ends. The "restore" conditions can be (equivalent, in alternative): • the detection of the device in Closed state • the detection of a minimum current value on the phases. The presence of Switch State Functionality is therefore NOT binding (Example: if the switch goes back to Open => the	2	Y
29196	29195	720B	1	Device Protection Relay Tripped ("III element", no phase indications)	The information reported here is maintained even when the condition that generated it ends. The "restore" conditions can be (equivalent, in alternative): • the detection of the device in Closed state • the detection of a minimum current value on the phases. The presence of Switch State Functionality is therefore NOT binding (Example: if the switch goes back to Open => the	2	Y
29197	29196	720C	1	RESERVED (returns "0")			
29198	29197	720D	1	Over-temperature P. Relay tripped	The information reported here is maintained even when the condition that generated it ends. The "restore" conditions can be (equivalent, in alternative): • the detection of the device in Closed state • the detection of a minimum current value on the phases. The presence of Switch State Functionality is therefore NOT binding (Example: if the switch goes back to Open => the	2	Y



Register	Register	Register	Dimension	Description	Note	Read	Write	Data
Number	Address	Address	[bit]			Function	Function	Storing
	(Dec)	(Hex)				Codes	Codes	
	` '	, ,				(Dec)	(Dec)	
				(no COILS availables)				



Register Number	Register Address (Dec)	Register Address (Hex)	Dimension [word]	Bit Position	Description	Туре	Scale	Unit	Range	Note	Read Function Code (Dec)	Data Storing
16385	16384	4000	6		State of Breaker							
16385 16386	16384 16385	4000 4001	1		RESERVED (returns error 84h) Operations counter					Total value, may not be zeroed	4	V
16387	16386	4001	1		Maximum Number of Operations		-			Not configurable	4	Y
16388	16387	4003	1		Breaker Features - Rated Current		1	Α		Hot configurable	4	Ý
16389	16388	4004	1		Breaker Features - Device Type and number of Poles						4	Y
				3÷0	Poles: number				1÷4		4	Y
				4 7÷5	Poles: neutral position (left(1)/right(0)) RESERVED (returns"0")						4	Y
				7 . 5	Type of device: Isolating switch (0)/ Automatic (1)						4	Y
				9	Type of device: Isolating Switch (6)/ Non Repulsive Breaker (1)						4	Ý
				15÷10	RESERVED (returns "0")						4	Y
16390	16389	4005	1		Tripping Features - Breaking capacity		0,01	kA			4	Y
29185	29184	7200	249		Three-phase Electric Protection							
29185 29195	29184 29194	7200 720A	10 1		RESERVED (returns error 84h) Overload P. relay (total) Tripped Counter (no phase indication)						4	Y
29196	29195	720B	1		Short circuit P. relay (total) Tripped Counter (no phase indication)						4	Y
29197	29196	720C	1		RESERVED (returns "8000h")						·	·
29198	29197	720D	1		Device Protection Relay (total) Tripped Counter ("III element", no phase						4	Y
					indications)							
29199 29200	29198 29199	720E 720F	1		RESERVED (returns "8000h")						4	V
29200	73133	/ ZU F	1		Over-temperature P. Relay (total) Tripped Counter Last Release data Buffer (Last Trip)			 			4	Y
20204	20202	7046			Last Release data Buffer (Last Trip): chronology, "year" (MSB) e "month"	i					7	
29201	29200	7210	1	<u></u>	(LSB)							
29202	29201	7211	1		Last Release data Buffer (Last Trip): chronology, "day" (MSB) e "hours" (LSB)	(1.65)						
29203	29202	7212	1		Last Release data Buffer (Last Trip): chronology, "minutes" (MSB) e "seconds"	(LSB)		m A 0C				
29204 29206	29203 29205	7213 7215	1	-	Last Release data Buffer (Last Trip): Interrupted current or temperature		-	mA, °C A/%		Expressed in "numeric coding"	4	Υ
29206	29205	7216	1		Protection settings detail which cause trip: Levels Protection settings detail which cause trip: Times			msec		Expressed in "numeric coding" Expressed in "numeric coding"	4	Y
29208	29207	7217	1		Protection settings detail which cause trip: Times Protection settings detail which cause trip: Options					Expressed in Humene county	4	Ý
				0	disabled(1)/active(0)						4	Y
				1	absolute value(1)/%In(0)						4	Y
				4÷2	I2t=k MEM OFF(001)/I2t=k MEM ON(000)					it's not present for device protection	4	Y
				7÷5 15÷8	RESERVED (returns "0") point of work, Ir multiple		-	 			4	Y
29209	29208	7218	1	15-8	Last Release data Buffer (Last Trip): "Tripped" type reading only bit reply - part I						4	ī
				0	Overload P. Relay Tripped Reply (no phase indication)						4	
				1	Short-circuit P. Relay Tripped Reply (no phase indication)						4	
				2	Device Protection Relay Tripped Reply ("III element", no phase indication)						4	
				3	Earth Fault P. Relay Tripped Reply						4	
				4	Over-temperature P. Relay Tripped Reply						4	
				5	Overload P. Relay Tripped Reply phase 1			ļ				
-				<u>6</u> 7	Overload P. Relay Tripped Reply phase 2 Overload P. Relay Tripped Reply phase 3		-	-	-			
				8	Overload P. Relay Tripped Reply N							
				9	Short circuit Instantaneus P. Relay Tripped Reply phase 1							
				10	Short circuit Instantaneus P. Relay Tripped Reply phase 2							
				11	Short circuit Instantaneus P. Relay Tripped Reply phase 3							
				12 13	Short circuit Instantaneus P. Relay Tripped Reply N Short circuit which may be delayed P. Relay Tripped Reply phase 1			 	 	 		
				14	Short circuit which may be delayed P. Relay Tripped Reply phase 1 Short circuit which may be delayed P. Relay Tripped which Reply phase 2		<u> </u>					
				15	Short circuit which may be delayed P. Relay Tripped Reply phase 3							
29210	29209	7219	1		Last Release data Buffer (Last Trip): "Tripped" type reading only bit reply - part II							
				0	Short circuit P. Relay Tripped which may be delayed Reply N	 		<u> </u>		ļ		
				2	Device Protection Relay Tripped Reply phase 1 ("III element")			 	 	 		
				3	Device Protection Relay Tripped Reply phase 2 ("III element") Device Protection Relay Tripped Reply phase 3 ("III element")		 	-				1
				4	Device Protection Relay Tripped Reply N("III element")		1					1
				5	Relay Tripped in mode "Main Setting"							
				6	Relay Tripped in mode "Dual Setting"							
				7	Overload Relay Tripped in mode "MEM=OFF"	 		<u> </u>		ļ		
				8	Short circuit which may be delayed Relay Tripped in mode "I ² t=k"		-	<u> </u>	<u> </u>			
				9	Short circuit which may be delayed Relay Tripped in mode "Logical Selectivity" (with delay Tm)							
-					Short circuit which may be delayed Relay Tripped in mode "Logical		 	†	 		 	
				10	Selectivity" (with delay SEL=High)		<u> </u>	<u> </u>	<u> </u>			
				11	Earth Fault P. Relay Tripped in mode "I ² t=k"							
				15÷12	RESERVED (returns "0")							
29211	29210	721A	10		Last Release data Buffer 1					See details in Last Release data Buffer (Last Trip)		



29221	29220	7224	10		Last Release data Buffer 2				See details in Last Release data Buffer (Last Trip)		
29231	29230	722E	10		Last Release data Buffer 3				See details in Last Release data Buffer (Last Trip)		†
29241	29240	7238	10		Last Release data Buffer 4				See details in Last Release data Buffer (Last Trip)		+
29251	29250	7242	10		Last Release data Buffer 5				See details in Last Release data Buffer (Last Trip)		++
								-	See details in Last Release data Buffer (Last Trip)		
29261	29260	724C	10		Last Release data Buffer 6				` ''		
29271	29270	7256	10		Last Release data Buffer 7				See details in Last Release data Buffer (Last Trip)		
29281	29280	7260	10		Last Release data Buffer 8				See details in Last Release data Buffer (Last Trip)		
29291	29290	726A	10		Last Release data Buffer 9				See details in Last Release data Buffer (Last Trip)		
29301	29300	7274	10		Last Release data Buffer 10				See details in Last Release data Buffer (Last Trip)		
29311	29310	727E	100		RESERVED (returns "8000h")						
29411	29410	72E2	1		G1 ("main setting") – overload: level		[A]/[%]				
29412	29411	72E3	1		G1 - overload: times		[msec]				
29413	29412	72E4	1		G1 - overload: options						1
29414	29413	72E5	2		G1 – short circuit which may be delayed: levels			A/%	Expressed in "numeric coding"	4	Y
29416	29415	72E7	1		G1 - short circuit which may be delayed: times			msec	Expressed in "numeric coding"	4	Υ
29417	29416	72E8	1		G1 - short circuit which may be delayed: options					4	Υ
				0	Bit0=disabled(1)/active(0)					4	Y
				1	absolute value(1)/%Ir(0)					4	Υ
				4÷2	curve t=k(001)/I2t=k(000)					4	Υ
				7÷5	RESERVED (returns "0")					4	Υ
				15÷8	Point of work for I2t curve, multiple of Ir)					4	Υ
29418	29417	72E9	4		RESERVED (returns "80000000h", "8000", "8000")						
29422	29421	72ED	2		G1 - device protection: levels			A/%	Expressed in "numeric coding"	4	Y
29424	29423	72EF	1		G1 - device protection: times			msec	Expressed in "numeric coding"	4	Y
29425	29424	72F0	1		G1 - device protection: options					4	Y
				0	disabled(1)/active(0)					4	Y
				1	absolute value(1)/%In(0)					4	Y
				15÷2	RESERVED (returns "0")					4	Y
29426	29425	72F1	6		RESERVED (all return "8000h")						
29432	29431	72F7	1		G1 – over-temperature protection: levels			°C	Expressed in "numeric coding"	4	Υ
29433	29432	72F8	1		G1 – over-temperature protection: times		<u> </u>	msec	Expressed in "numeric coding"	4	Y
20481	20480	5000	3		Three-phase Electric Measurement				Ibyproceed on "numeric coding", without meetic		
20481	20480	5000	1		Phase 1 Current Value (R)	unsigned integer		Α	Expressed on "numeric coding"; without mark (fixed more significant bit = 0)	4	
20482	20481	5001	1		Phase 2 Current Value (S)	unsigned integer		Α	Expressed on "numeric coding"; without mark (fixed more significant bit = 0)	4	
20483	20482	5002	1		Phase 3 Current Value (T)	unsigned integer		А	Expressed on "numeric coding"; without mark (fixed more significant bit = 0)	4	
32769	32768	8000	1		Single-channel Thermal Measurement						
32769	32768	8000	1		Sensor 1 Temperature Value	signed integer		°C	Expressed in "numeric coding"	4	

Register	Register	Register	Dimension	Bit Position	Description	Туре	Scale	Unit	Range	Note	Read	Write	Data
Number	Address	Address	[word]								Function	Function	Storing
	(Dec)	(Hex)									Codes	Codes	
											(Dec)	(Dec)	
					(no HOLDING REGISTERS availables)								

