



Key fob switch

YW4548 - YG4548 - YD4548
 YW4549 - YG4549 - YD4549
 YW4548M2 - YG4548M2 - YD4548M2
 YW4549M2 - YG4549M2 - YD4549M2



Y_4548 - Y_4549



Y_4548M2 - Y_4549M2

Use

Key fob switch to switch ON lights and devices in hotel rooms. To be completed with front cover in the desired look.

Connection


Terminal type: screw clamp
 Terminal capacity: 2 x 2,5 mm²
 Stripping length: 8 mm
 Compatible with flexible or rigid cables

Range

Designation	Item
Key fob switch with RFID technology recognition - 3m	☐ YW4548
	☐ YG4548
	☐ YD4548
Key fob switch - 3m	☐ YW4549
	☐ YG4549
	☐ YD4549
Key fob switch with RFID technology recognition - 2m	☐ YW4548M2
	☐ YG4548M2
	☐ YD4548M2
Key fob switch - 2m	☐ YW4549M2
	☐ YG4549M2
	☐ YD4549M2

Colors: ☐ White ☐ Stone ☐ Dark

Overall dimensions (mm)



	A	B	C	D
J_4548 - J_4549	68.7	45.1	32.6	22.3
J_4548M2 - J_4549M2	61	47	32.6	29.1

Technical characteristics

- **Protection index**
 Penetration by solid bodies/liquid: IP20D (considering a complete installation, including cover plate)
- **Mechanical characteristics**
 Impact test: IK 04
- **Material characteristics**
 Material:
 Case and Key cover: PC (Polycarbonate)
 Halogen free.
 UV resistant.
 Self-extinguishing:
 850° C / 30 s for insulating parts holding live parts in place
 650° C / 30 s for other parts made of insulating materials
- **Electrical characteristics**
 Voltage: 230 VAC
 Current: 30VA
- **Climatic characteristics**
 Storage temperature: - 10° C to + 70° C
 Use temperature: - 5° C to + 35° C

Cleaning

Clean the surface with a cloth.
 Do not use acetone, tar-removing cleaning agents or trichloroethylene.
Caution: Always test before using special cleaning products.

Standards and approvals

Compliance with standards IEC/EN 60669-1-2
 Refer to e.catalogue.