











	110 / 240 V~
	50 / 60 Hz
	2 x 1,5 mm ² - 1 x 2,5 mm ²
	-5°C / +45°C
	 PIR
	300 lux
	15 min
	12 m








									
									
									
230 V~	2000 W	8,5 A	1000 VA	4,3 A	1000 VA	4,3 A	10x(2x36 W)		4,3 A
110 V~	1000 W		500 VA		500 VA		5x(2x36 W)		
									
									
230 V~	250 W	1 A	250 W	1 A	250 W	1 A	500 VA		2,1 A
110 V~	125 W		125 W		125 W		250 VA		

			
			
230 V~	500 VA	2,1 A	I max. ≤ 2,1A
110 V~	250 VA	maxi	
U ≤ 30 V=	2,1 A maxi		

















 Auto ON/OFF



Manual ON / Auto OFF



www.legrandoc.com



- LED Learn
- Learn LED
- Boutton Learn
- Learn Button

- LED de détection
- Motion led

- Détecteur/capteur PIR
- PIR sensor

- Cellule de luminosité
- Daylight sensor

	5 - 1275 lux
	5 sec - 59 min 59 sec
	25 - 50 - 75 - 100 %
Mode	Auto - Manual - Walktrough



OK



NO



0 882 30



0 882 35