


## Cat.6 U/UTP LSZH advanced cable for local networks

Catalogue number(s) : 0 328 66




### 1. USE

Cable for high-speed VDI transmission networks

802.3 bt PoE++ up to type 4 applications compatible according to installation standards ISO/IEC 14763-2 : 2019 and EN 50174-2 : 2018

### 2. DESCRIPTION



### 3. MARKING AND PACKAGING

Marking of Legrand cables

- LEGRAND
- Catalogue number
- Number of pairs
- Gauge
- Type
- Impedance
- Type of sleeve
- Category
- Conformity to standards
- EUROCLASS
- Velocity of propagation
- Traceability
- Measurement (remaining length in metres).

Complementary marking (on label)

- Designation
- Made in....

### 4. PERFORMANCE AT 250 MHZ (STAND. ANSI/TIA 568.2-D)

Reference	0 328 66
Maximum attenuation (dB/100 m)	32,8
Minimum NEXT (dB)	38,3
PS NEXT (dB)	36,3
ACRF (dB / 100 m)	19,8
PS ACRF (dB / 100 m)	16,8
Return Loss (dB)	17,3

### 5. TECHNICAL AND MECHANICAL FEATURES

Catalogue number	0 328 66
Type	U/UTP
Type of sleeve	LSZH
Number of pairs	4
Assembly	Pairs
Diameter over insulation (mm)	1,02 ± 0,05
Average nominal diameter of the cable (mm)	6,2 ± 0,3
Weight of cable (kg/km)	40
Min. bending radius when laying (mm)	>26
AWG gauge*	23

\* According to UL 444 ed.3 table 4

**6. ELECTRICAL FEATURES AT 20°C**

Catalogue number	0 328 66
Type	U/UTP
Maximum linear resistance (ohm/km)	95 *
DC dielectric strength	1 KV / 1 min *
Minimum insulation resistance (Mohm.km)	5000
Minimum propagation speed	≥65 %
Characteristic impedance at 100 MHz	100 ±5Ω

\* According to standard IEC 61156-5

**7. ORDERING INFORMATION**

Catalogue number	0 328 66
Type	
Colour	Blue RAL 5015
Pack (m)	305
Packaging	Box

**8. ENVIRONMENTAL FEATURES**

Transport and storage temperature: -20 at + 60 °C  
 Storage temperature before installation: 10°C during 24h (if stock ≤ 5°C)  
 Usage temperature: - 20 to + 60 °C

Fire rating:EN 50399, IEC 60332-1-2, EN 60332-1-2, IEC 60332-3-22  
 Smoke density : IEC 61034-2, EN 61034-2  
 Toxicity of fire effluent : IEC 60754-2, EN 60754-2

EUROCLASS EN 13501-6 = Class Dca - s1a, d2, a1  
 Also compliant with Eca

**9. STANDARDS AND APPROVALS**

Cat 6, 250 MHz  
 Electrical performances and characteristics :  
 - ANSI/TIA 568.2-D  
 - EN 50173-1  
 - EN 50288-6-1  
 - ISO/IEC 11801 (ed. 2.2)  
 - IEC 61156-5  
 IEEE 802.3bt : PoE++