




	RJ 45 (PoE/PoE+ class 0) or • Screw terminal block (27_50 V~/V=)
	RJ 45 IP Network
X =	x = 8
	-5°C → +45°C
	IEC 60669-2-1









- Alimentation
 - Power
- 27-50 V~/V= **ou** PoE/PoE+
 6 W **or**



		A	B	C	110/230 V~ 50/60 Hz		E					
		1 ₁ 2 ₁	1 ₁ 2 ₁	1 ₁ 2 ₁ 3 ₁ 4 ₁ L			E ₁ 2 ₁ L	Nc	Ne	μ		
A - B	230 V~								250 VA	1,1 A	250 VA	1,1 A
	110 V~								125 VA		125 VA	
	12 - 48 V~/V=								13 - 52 VA	1,1 A	13 - 52 VA	1,1 A
C	230 V~	160 VA	500 VA	500 VA	4 (2 x 36) W	160 VA	160 VA	1000 W	500 VA	500 VA		
	110 V~	80 VA	250 VA	250 VA	2 (2 x 36) W	80 VA	80 VA	500 W	250 VA	250 VA		
		0,7 A	2,1 A	2,1 A	1,7 A	0,7 A	0,7 A	4,3 A	2,1 A	2,1 A		
E	230 V~	500 VA	1000 VA	1000 VA	10 (2 x 36) W	500 VA	500 VA	3680 W	500 VA	500 VA		
	110 V~	250 VA	500 VA	500 VA	5 (2 x 36) W	250 VA	250 VA	1760 W	250 VA	250 VA		
		2,1 A	4,3 A	4,3 A	4,3 A	2,1 A	2,1 A	16 A	2,1 A	2,1 A		







Inputs	G1	G2	G3	G4	G5	G6	G7	G8
Outputs	A1/A2	B1/B2	C1	C2	C3	C4	E1	E2
Action	UP/ DOWN	UP/ DOWN	ON/ OFF	ON/ OFF	ON/ OFF	ON/ OFF	ON/ OFF	ON/ OFF



www.legrandoc.com