


PoE injector with 1 port


Cat. No(s): 0 327 37



1. USE

For supplying Power over Ethernet (PoE) to peripherals such as Wi-Fi access points, IP cameras, etc
 Conforming to standard IEEE 802.3 af
 1 input/1 output
 Connected directly to the patch panel

2. POSITIONING



3. DIMENSIONS

Cat. No.	Length	Width	Height
0 327 87	160 (mm)	64 (mm)	36 (mm)

4. TECHNICAL CHARACTERISTICS

Voltage	Input voltage	100 VAC~240 VAC
	Input data	RJ45
	PoE output	RJ45
PoE	Electricity supply type	MIDSPAN
	Output power	54 VDC/30 Watts
	Power	Pair: 1/2(+); 3/6 (-)
Ethernet port	Port output type	RJ45
	Transmission speed	10/100/1000 Mbps
	Transmission medium	Cat 5/5E/6 cable
	Distance	100 m maximum
LED	Power supply LED	Red
	PoE LED	Orange
Protection	Overvoltage	PoE power: 1 kV (residual current mode), 2 kV (common mode) 1.2/50 μ s, 8/20 μ s Ethernet: 2 kV (residual current mode), 6 kV (common mode) 10/7000 μ s
	ESD	Contact discharge 1a level 3 Remote discharge 1b level 3 IEC 61000-4-2
Environment	Operating temperature	-10°C/+55°C
	Storage temperature	-40°C/+85°C
	Humidity	0 - 90%
Mechanism	Material	ABS plastic
	Colour	Black
	Weight	200 g