

MODBUS TABLE ORGANIZATION

Starting Address of the Group Registers (Dec)	Starting Address of the Group Registers (Hex)	System Version (Release)	System Version (Build)	Group Name (Text)	Group Code (Hex)	Group Complexity (Hex)	Group Version (Hex)	Object Code
18688	4900	01	16	Contacteur Command	63 01	10	01 00	
18688	4900	01	16	Contacteur Command configuration	63 01	10	01 00	

MODBUS PROTOCOL DETAILS

Function Code (Dec)	Exception Codes (Dec)	Data Encoding
2 (Read Discrete Inputs)	1, 2, 3	"Big Endian" (most significant byte first)
1 (Read Coils)	1, 2, 3	"Big Endian" (most significant byte first)
5/15 (Write Single/Multiple Coils)	1, 2, 3	"Big Endian" (most significant byte first)
4 (Read Input Registers)	1, 2, 3	"Big Endian" (most significant byte first)
3 (Read Holding register)	1, 2, 3	"Big Endian" (most significant byte first)
6/16 (Write Single/Multiple Holding register)	1, 2, 3	"Big Endian" (most significant byte first)

MODBUS OVER SERIAL DETAILS

Physical Layer	Transmission Modes	Device Addressing	Baud Rates (bit/s)	Data Bits	Data bits transmission sequence	Parity	Stop Bits
standard EIA/TIA 485 (RS-485) two-wire configuration	RTU	1÷247	programmable (1200, 2400, 4800, 9600, 19200, 38400)	8	Least significant bit first	NONE	1

MASTER/SLAVE COMMUNICATION TIMING

Timer Description	Timer Value (msec)
Inter-character time-out	< 1,5 character times
Response delay (from master request)	-
Delay Time (between two master transmissions)	-

REFER ALSO TO: www.modbus.org - MODBUS over serial line specification and implementation guide V1.02
 - MODBUS APPLICATION PROTOCOL SPECIFICATION V1.1b

NOTE: File and printed copies of this document are not subject to document change control.



Register Number	Register Address (Dec)	Register Address (Hex)	Dimension [bit]	Description	Read Function Codes (Dec)	Data Storing
-----------------	------------------------	------------------------	-----------------	-------------	---------------------------	--------------

Register Number	Register Address (Dec)	Register Address (Hex)	Dimension [bit]	Description	Note	Read Function Codes (Dec)	Write Function Codes (Dec)	Data Storing
18689	18688	4900	2	Contactor Command				
18689	18688	4900	1	Energize		1	5,15	
18690	18689	4901	1	De-energize		1	5,15	



Register Number	Register Address (Dec)	Register Address (Hex)	Dimension [word]	Bit Position	Description	Type	Scale	Unit	Range	Note	Read Function Code (Dec)	Data Storing
-----------------	------------------------	------------------------	------------------	--------------	-------------	------	-------	------	-------	------	--------------------------	--------------



Register Number	Register Address (Dec)	Register Address (Hex)	Dimension [word]	Bit Position	Description	Type	Scale	Unit	Range	Note	Read Function Codes (Dec)	Write Function Codes (Dec)	Data Storing
18689	18688	4900	1		Contactor Command configuration								
18689	18688	4900	1		Command configuration					(3)	3	6,16	
18690	18689	4901	1		Activation time (if impulsive)		0,1	sec			3	6,16	
18691	18690	4902	1		Delay on command		0,1	sec			3	6,16	

NOTE 3) BIT 0: Normally Open = 0, Normally Closed = 1
 BIT 1-2: impulsive = 00, maintained = 10, toggle = 01
 BIT 3: 0 = independent, 1 = interlocked
 BIT 4-15: not used

