

PIR switch sensor

Catalogue Number(s): 0 488 04

Light level cell

IR receiver LED

tool or remote

control)

LED

tool)

Protective cover

Ó

(for configuration


IR transmission

(for configuration

Green

detection

indicator



LEARN button

LEARN LED

indicator

Sensor/PIR

sensor

programming

0

(M)

2 A max.

85 A

2000 W

1000 W

230 V~

110 V~

 $U \le 30 V_{=}$

Green

It is equipped with a "presence" output for ventilation or lighting control. This output is separate from the level of light. Motion sensor with 360° detection angle. Detection type: infrared (PIR) Mounting type: ceiling 2. TECHNICAL CHARACTERISTICS Voltage: 100 - 240 V~ Frequency: 50/60 Hz No-load power consumption: 0.8 W

Output via normally open contact connected to the phase Wiring: 2 x 2.5 mm² Drilling diameter: 85 mm without flush-mounting box 85 mm with flush-mounting box Weight: 114 g

the detection of movement in the surveillance zone.

Impact resistance: IK04

1. USE

Penetration by solid and liquid matter: IP20 (unmounted) IP41 (mounted)

Usage temperature: - 5°C to + 45°C Storage temperature: - 20°C to + 70°C

		ß	∞ 💭 + 💬	3 ● + ●	©	©	©	ļ				>	
	-Ķ	<u>}</u> -						\otimes	⊐∎⊗		-Å	-	
230 V~	2000 W	0.5.4	1000 VA		10x(2x36\	· ·	500 VA	214	1000 VA		500 VA	214	L
110 V~	1000 W	8.5 A	500 VA	4.3 A	5x(2x36 V	4.3 A	250 VA	2.1 A	500 VA	4.3 A	250 VA	2.1 A	l max. ≤ 2A
① Halogen bulb							:				6	<u>س</u>	

2 ELV halogen bulb with separate electronic ballast

③ ELV halogen bulb with separate ferromagnetic ballast

④ Fluorescent tube with separate ferromagnetic ballast

⑤ ELV fluorescent tube with separate electronic ballast

© Compact fluorescent bulb with built-in electronic ballast

 ${\ensuremath{\mathbb O}}$ Compact fluorescent bulb with separate ferromagnetic ballast

⑧ Compact fluorescent bulb with separate electronic ballast


Ontactor


¹¹ Motor

Created: 18/01/2013


3. DIMENSIONS


Without protective cover





With protective cover







4. CONNECTION

Number of terminals: 6 Type of terminals: automatic Terminal capacity: 2 x 2.5 mm² Stripping length: 8 mm

■ 4.1 Wiring with auxiliary control:






Wiring






4. CONNECTION (continued)


4.2 Wiring for a single load connected in parallel



4.3 Wiring for several loads connected in parallel



Updated: 01/09/2022



4/8

7. OPERATION

Manual ON/Automatic OFF mode

Pressing the auxiliary control allows the load to be switched on or off manually. If the control is not pressed, the sensor will cut off the load at the end of the time delay or when the light level threshold has been reached.

Auto ON/OFF mode:

The load will be switched on and off automatically.

Option: It is possible to control the sensor by infrared remote control using Cat. Nos. 0 882 00/01/20/31/32/33.

■ 7.1 More than one sensor and more than one load

The products can be synchronised in two steps:


- one long press (>1s) - all the sensors (S) change to ON

- one short press - all the sensors (S) invert their state from OFF to ON and ON to OFF

⊗ L1 OFF ⊗ L2 OFF ⊗ Ln OFF	S1 OFF	PB S 1s	>X L1 ON >X L2 ON >X Ln ON	S1 ON S2 ON Sn ON
>⊗< L1 ON >⊗< L2 ON >⊗< Ln ON	\$1 ON \$2 ON \$52 ON \$50 Sn ON	PB 	⊗ L1 OFF ⊗ L2 OFF ⊗ Ln OFF	S1 OFF S2 OFF
≥X L1 ON ⊗ L2 OFF ⊗ Ln OFF	S1 ON S2 OFF Sn OFF	PB +1s	⊗ L1 OFF >⊗< L2 ON >⊗< Ln ON	S1 OFF
×× L1 ON ⊗ L2 OFF ⊗ Ln OFF	 \$1 ON \$2 OFF \$n OFF 	PB + <1s	⊗ L1 OFF ⊗ L2 OFF ⊗ Ln OFF	S1 OFF S2 OFF Sn OFF
>∑< L1 ON ⊗ L2 OFF ⊗ Ln OFF	\$1 ON \$2 OFF \$5 Sn OFF	PB >1s	>X L1 ON >X L2 ON >X L1 ON	sı on 🖨 sz on 🎝 Sn on

7. OPERATION (continued)

■ 6.1 Several sensors connected to a single load



Technical data sheet: S000074405EN_3

Updated: 01/09/2022

Created: 18/01/2013

8. SETTINGS

8.1 Detection parameters

Sensor parameter Time delay		Default value	Modifiable parameters	Configuration tools	
				0 882 30	0 882 35
		15	3, 5, 10, 15, 20 min	-	 ✓
Time	delay	15 min	0 - 59 min 59 s	 ✓ 	-
Sensitivity		PIR (very high)	Low, medium, high, very high	~	~
Modes	Auto on/Auto off	Inactive	Activate/ Deactivate	~	~
	Walk-through mode	Active	Activate/ Deactivate	~	~
-	Manual on/ Auto off	Inactive	Activate/ Deactivate	~	~
۰. ۲	Initial	PIR	Non-modifiable	~	-
Detection system	Maintain	PIR	Non-modifiable	~	-
Restart		PIR	PIR, Deactivate	~	-
Alarm		Inactive	Activate/ Deactivate	~	-

(b) **Time delay:** Length of time the load is on after detection.

Sensitivity: Detection range setting.

Modes:

🚯 Auto on/Auto off mode:

Automatic switch-on:

On detection of presence if there is insufficient natural light. Automatic switch-off:

If no presence is detected and at the end of the set time delay.
Or if there is sufficient natural light (regulation activated)
Another detection causes automatic switch-on if there is insufficient light.

Walk-through mode:

- If no presence is detected in the 20 seconds following an initial detection, the product will cut off the load after 3 minutes.
- If another presence is detected in the 3 minutes following initial detection, the device will cut off the load at the end of the set time delay.

Manual on/Auto off mode:

Manual switch-on, automatic switch-off:

- When no presence is detected and at the end of the set time delay.

After switch-off, any new detection within a 30 second period triggers an automatic switch-on. The Restart function must be activated. After 30 seconds the device is switched on via a manual switch.

Detection system:

Initial detection: The load is switched on as soon as the first detection occurs if the natural light level is below the light level threshold.

Maintain: The load remains active if another presence is detected.

Restart: In manual mode. After switch-off, any new detection within a 30 second period triggers an automatic switch-on. After 30 seconds the device must be switched on manually.

Possible in Manual on/Auto off mode only.

Alarm: An audible signal is emitted before switch-off (1 minute before, then 30 seconds, then 10 seconds).

8. SETTINGS (continued)

8.2 Light parameters

Senso	or parameter	Default value	Modifiable parameters	Configuration tools	
				0 882 30	0 882 35
Light	level threshold	500 lux	20, 100, 300, 500, 1000 lux	-	~
5			0 - 1275 lux	✓	-
70	Calibration	-	0 - 99995 lux	1	-
Advanced mode	Regulation	Active	Activate/ Deactivate	~	-
ΡЧ	Light contribution	Auto	Auto - 1275 lux	~	-

 $\frac{1}{2}$ ight level threshold: Value at which the load comes on if the natural light level is less than the setting.

Eye function: Value 0 (eye on configuration tool 0 882 30) is used to save the ambient light level in the room as the light level threshold.

Advanced mode:

- Calibration: The ambient light level measured with a luxmeter must then be transmitted to the sensor.
- Regulation: Automatic switch-off of the load 10 minutes after the light level threshold is exceeded with an additional safety threshold (to avoid lights switching off at the wrong moment).

Light contribution: Quantity of additional lux provided by the load being switched on.

When the light contribution parameter is set to "Auto" (value 0) on the configuration tool Cat. No. 0 882 30, the sensor automatically calculates the light contribution.

■ 8.3 Modifying the parameters using the configuration tools

• 0 882 40: Configuration gateway and Legrand Close Up application. The Close Up application is available on the Apple Store and the Play Store






The detector functions are controlled by a number of parameters which can be changed or programmed by an infrared configurator.

In combination with configuration tool 0 882 40, the Legrand Close Up smartphone app can be used to view and modify all the detector parameters with online help.

Point the infrared configuration tool at the detector and send the

necessary programming commands to the unit as indicated in the table below.

For more information about setting parameters, refer to the data sheet for the configuration gateway Cat. No. 0 882 40.



Created: 18/01/2013


8. SETTINGS (continued)

8.3 Modifying the parameters using the configuration tools (continued)

0 882 30: Configuration tool

When the sensor receives an IR command via a configuration tool, it emits a beep confirming that the modification has been taken into account.


For more information about setting parameters, refer to the data sheet for the configuration tool Cat. No. 0 882 30.



- Restore to factory settings:

1st press: Short press on LEARN: the LED flashes slowly. 2nd press: Press and hold down LEARN for 10 seconds until the LED flashes quickly.

9. PERFORMANCE




		Sensitivity Low (25%)	Sensitivity Medium (50%)
		Ø (m)	Ø (m)
	2.5	4	6
E)	3	5.5	6.5
ght	4	6.5	7.5
Height (m)	5	6	10.5
-	6	4	5.5

		Sensitivity High (75%)	Sensitivity Very high (100%)
		Ø (m)	Ø (m)
_	2.5	6.5	8
<u></u>	3	8.5	11.5
ght	4	12.5	14
Height (m)	5	12	16.5
-	6	8.5	12.5

9. PERFORMANCE (continued)





		Sensitivity Low (25%)	Sensitivity Medium (50%)
		Ø (m)	Ø (m)
	2.5	2.5	4
E	3	3.5	4
ght	4	4	5
Height (m)	5 4		6.5
_	6	2.5	3.5

		Sensitivity High (75%)	Sensitivity Very high (100%)
		Ø (m)	Ø (m)
_	2.5	4	5
Ē	3	5	7
ght	4	8	9
Height (m)	5	7.5	10
	6	5	8

Technical data sheet: S000074405EN_3

Updated: 01/09/2022

10. CARE

Keep the lens clean.

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene. Resistant to the following products: - Hexane (EN 60669-1)

- Methylated spirit
 - Soapy water
 - Diluted ammonia
 - Bleach diluted to 10%
 - Window-cleaning products

Note:

Always test before using other special cleaning products.

11. STANDARDS

Directive: CE

Product standards: IEC 60669-2-1 Environmental standards:

- European Directive 2002/96/EC:

WEEE (Waste Electrical and Electronic Equipment) - European Directive 2002/95/EC:

RoHS (Restriction of Hazardous Substances)

12. TROUBLESHOOTING

PROBLEM	CAUSES	SOLUTIONS
Lighting stays on when there is no-one present	Sources of interference, such as draughts,	1- Reduce the sensitivity level
	vibration or radiators, may cause nuisance tripping	2- If the interference continues: using the configuration tool, go into the Detection system parameters, select Maintain and then choose PIR and US
		3- If the interference still continues, move the sensor away from the source(s) of interference
Lighting does not switch off during the day	Regulation function not active	Activate the regulation function
when there is an adequate level of natural light	Light level threshold set too high	Reduce the light level threshold
	Light contribution too high	Check that the sensor is positioned correctly in relation to the window
		Decrease the power of the luminaires
Lighting switches off when there are people	Time delay too short	Increase the time delay
present and the natural light level is not	Detection sensitivity too low	10 to 1 minutes is recommended for work
adequate (darkness)	Light level threshold too low	areas
		Increase the sensitivity
		Move the sensor closer to the work area
		Increase the threshold