


PIR lighting management sensor - Outdoor version



CONTENTS	Page
1. Use	1
2. Technical characteristics	1
3. Dimensions	2
4. Connection	2
5. Removal	3
6. Installation	4
7. Operation	5
8. Settings	6
9. Performance	8
10. Care	9
11. Standards and certifications	9
12. Troubleshooting	9

1. USE

This device allows a light source to be controlled automatically by detecting movement in a monitored area.

It can be installed outdoors (car park, driveway) and also in places like cellars, test rooms, laboratories.

Motion sensors with 270° and 360° detection angle.

Detection type: infrared (PIR) Mounting type: ceiling, wall

2. TECHNICAL CHARACTERISTICS

Voltage: 110 - 240 V~ Frequency: 50/60 Hz

No-load power consumption: 0.6 W

Output via normally open contact connected to the phase


Wiring: 2 x 2.5 mm² Number of terminals: 4 Terminal type: screwless Stripping length: 8 mm Weight: 200 g Impact resistance: IK04


Penetration by solid and liquid matter: IP55 Usage temperature: - 25°C to + 45°C Storage temperature: - 25°C to + 70°C

2. TECHNICAL CHARACTERISTICS (continued)

Products approved for 40,000 operations


Mains zero breaking: in order to limit the effect of induced currents on cut-off relays by fluorescent loads in particular, this sensor breaks the voltage at mains zero. Switching occurs when the voltage is at point 0 which ensures a longer life for sources and for the sensor.






- 1 Halogen bulbs
- 2 ELV halogen, compact fluorescent and fluorescent bulbs with separate electronic ballast
- 3 ELV halogen, compact fluorescent and fluorescent bulbs with separate ferromagnetic ballast
- 4 Fluorescent tubes
- ${\bf 5}$ Compact fluorescent bulbs with built-in electronic ballast
- 6 Compact fluorescent bulbs with built-in ferromagnetic ballast
- 7 LED bulbs

- 8 Contactor
- 9 Motor




3. DIMENSIONS



4. CONNECTION


■ 4.1 Wiring with auxiliary control:







■ 4.2 Wiring for several loads connected in parallel



Technical data sheet: S000081482EN_2


Updated: 06/09/2022

Created: 31/03/2014 La legrand


CONTENTS 2/9

4. CONNECTION (continued)

■ 4.3 Wiring for a single load connected in parallel




■ 4.4 Wiring with a timer



With this wiring, the configuration tool must be on "Pulse" (see paragraph 8. Settings).


5. REMOVAL





Created: 31/03/2014 La legrand

6. INSTALLATION


■ 6.1 Sensor positioning








■ 6.2 Recommended light exposure









6. INSTALLATION (continued)

■ 6.3 Fitting













Attention:

Break the tabs to allow water to drain away.










Technical data sheet: S000081482EN_2


Updated: 06/09/2022


Created: 31/03/2014 **L1 legrand**


6. INSTALLATION (continued)

■ 6.3 Fitting (continued)









7. OPERATION

Manual ON/Auto OFF mode:

Pressing the auxiliary control allows the load to be switched on or off manually. If the control is not pressed, the sensor will cut off the load at the end of the time delay or when the light level threshold has been reached.

Auto ON/OFF mode:

The load will be switched on and off automatically.

Option: It is possible to manage the sensor using infrared remote control: Cat. Nos. 0 882 20/31.

■ 7.1 More than one sensor and more than one load

The products can be synchronised in two steps:

- one long press (>1s) all the sensors (S) switch to the ON state
- one short press all the sensors (S) inversion of OFF to ON or ON to OFF

⊗L1 OFF ⊗L2 OFF ⊗Ln OFF	S1 OFF S2 OFF Sn OFF	PB <1s	L1 ON L2 ON Ln ON	S1 ON S2 ON Sn ON
L1 ON L2 ON Ln ON	\$ 51 ON \$ 52 ON \$ 5n ON	PB <1s	⊗L1 OFF ⊗L2 OFF ⊗Ln OFF	S1 OFF S2 OFF Sn OFF
L1 ON L2 OFF Ln OFF	S1 ON S2 OFF Sn OFF	PB <1s	⊗L1 OFF	S1 OFF S2 ON Sn ON
L1 ON L2 OFF Ln OFF	S1 ON S2 OFF Sn OFF	PB >1s + <1s	⊗L1 OFF ⊗L2 OFF ⊗Ln OFF	S1 OFF S2 OFF Sn OFF
L1 ON L2 OFF Ln OFF	S1 ON S2 OFF Sn OFF	PB >1s	L1 ON	S1 ON S2 ON Sn ON

7. OPERATION (continued)

■ 7.2 Several sensors connected to a single load

⊗L OFF	S1 OFF S2 OFF Sn OFF	PB <1s	≥⊠ CL ON	Ssi ON Ssz ON Sn ON
>X L ON	GS1 ON GS2 ON GSn ON	PB <1s	⊗L OFF	Ss OFF
>>> L on	GS1 ON GS2 OFF GSn OFF	PB <1s	≥⊠ L ON	S1 OFF S2 ON Sn ON
>X L ON	GS1 ON GS2 OFF GSn OFF	PB >1s + + <1s	⊗L OFF	Ss OFF
>X L ON	GS1 ON GS2 OFF GSn OFF	PB >1s	≥⊠ CL ON	SSI ON SSZ ON SSN ON

8. SETTINGS

■ 8.1 Detection parameters

Sensor parameter		Default value	Modifiable parameters	Configuration tools	
				0 882 30	0 882 35
T:	4-1	15 min	3, 5, 10, 15, 20 min	-	✓
Time	delay	15 MIN	5 s - 59 min 59 s	✓	-
Sensi	tivity	PIR (very high)	Low, medium, high, very high	✓	✓
Auto on/Auto off		Inactive	Activate/ Deactivate	✓	✓
Modes	Walk-through mode	Active	Activate/ Deactivate	✓	✓
Manual on/Auto off		Inactive	Activate/ Deactivate	✓	~
ם כ	Initial	PIR	Not modifiable	✓	-
Detection system	Maintain	PIR	Not modifiable	✓	_
Restart PI		PIR	PIR, Deactivate	✓	_
Alarn	n	Inactive	Activate/ Deactivate	✓	-

- Time delay: Length of time the load is on after detection occurs.
- Sensitivity: Detection range setting.
- Pulse function: Value 0 (on configuration tool 0 882 30) is used to set the time delay on the timer.

For timer operation, activate the pulse function with the configuration tool 0 882 30. Go to Sensor parameter\time delay, then set the time delay to 00 h 00 min 00 s: the Pulse icon appears on the screen, then send the setting to the sensor and the PULSE function will be activated, finally set the time delay on the timer (10 minutes max).

Modes:

Auto on/Auto off mode:

Comes on automatically:

- At the detection of a presence if there is an insufficient natural level of

Turns off automatically:

- If no presence is detected and at the end of the time delay set.
- Or if the natural light level is sufficient (regulation activated).
- Any new detection triggers an automatic switch-on if there is insufficient light.

(F2) Walk-through mode:

- If no presence is detected in the 20 seconds following an initial detection, the product will cut off the load after 3 minutes.
- If another presence is detected in the 3 minutes following initial detection, the device will cut off the load at the end of the set time

Manual on/Auto off mode:

Manual switch-on, automatic switch-off:

- When no presence is detected and at the end of the set time delay. After switch-off, any new detection within a 30-second period triggers an automatic switch-on. The Restart function must be activated. After 30 seconds the device is switched on via a manual control.

Detection system:

Initial detection: The load is switched on as soon as the first detection occurs if the natural light level is below the light level threshold.

Maintain: The load remains active if another presence is detected.

Restart: In manual mode. After switch-off, any new detection within a 30-second period triggers an automatic switch-on.

After 30 seconds the device must be switched on manually.

Alarm: an audible signal is emitted before switch-off (1 minute before, then 30 seconds, then 10 seconds).

Created: 31/03/2014 LT legrand

Technical data sheet: S000081482EN_2 Updated: 06/09/2022

8. SETTINGS (continued)

■ 8.2 Light parameters

Sensor parameter		Default value	Modifiable parameters	Configuration tools	
				0 882 30	0 882 35
Light level threshold		150 lux	20, 100, 300, 500, 1000 lux	-	✓
			5 - 1275 lux	✓	-
-	Calibration	-	0 - 99,995 lux	✓	-
Advanced mode	Regulation	Active	Activate/ Deactivate	✓	-
Ad	Light contribution	Auto	Auto - 1275 lux	✓	-

- : Light level threshold: Value at which the load comes on if the natural light level is less than the setting.
- **Eye function:** Value 0 (eye on configuration tool 0 882 30) is used to save the ambient light level in the room as a light level threshold.

Advanced mode:

- (Calibration: The ambient light level measured with a luxmeter must then be transmitted to the sensor (see data sheet Cat. No. 0 882 30).
- Regulation: Automatic switch-off of the load 10 minutes after the light level threshold is exceeded with an additional safety threshold (to avoid lights switching off at the wrong moment).

Light contribution: Quantity of additional lux brought in by the load being switched on.

When the light contribution parameter is set to "Auto" (value 0) on configuration tool 0 882 30, the sensor automatically calculates the light contribution.

■ 8.3 Modifying the parameters using the configuration tools

• 0 882 40: Configuration gateway and Legrand Close Up application. The Close Up application is available on the Apple Store and the Play Store








The detector functions are controlled by a number of parameters which can be changed or programmed by an infrared configurator. In combination with configuration tool 0 882 40, the Legrand Close Up smartphone app can be used to view and modify all the detector parameters with online help.

Point the infrared configuration tool at the detector and send the necessary programming commands to the unit as indicated in the table

For more information about setting parameters, refer to the data sheet for the configuration gateway Cat. No. 0 882 40.

8. SETTINGS (continued)

■ 8.3 Modifying the parameters using the configuration tools



- 0 882 35: Simplified configuration tool
- 0 882 30: Advanced configuration tool

When the sensor receives an IR command via a configuration tool, it emits a beep acknowledging the modification.

For more information about setting parameters, refer to the data sheet for the configuration tool Cat. No. 0 882 30 and the lighting management sensor guide.

- Restore to factory settings:


1st press: Short press on LEARN, the LED flashes slowly. 2nd press: Hold down LEARN for 10 seconds until the LED flashes






Technical data sheet: S000081482EN_2 Updated: 06/09/2022

9. PERFORMANCE



■ 9.1 Radial movement ←





Installation height: 2.5 m and 4 m

	Sensitivity Low (25%)		Sensitivity Medium (50%)		Sensitivity High (75%)		Sensi Very hig	tivity h (100%)
	a (m)	b (m)	a (m)	b (m)	a (m)	b (m)	a (m)	b (m)
2.5	2	6	3	6	4	6	4	6
4	2	7	3	7	4	8	4	8

9. PERFORMANCE (continued)

■ 9.2 Tangential movement





Installation height: 2.5 m and 4 m

mstandion neight 215 m and 1 m								
		tivity (25%)	Med	tivity lium)%)	Sensitivity High (75%)		Sensitivity Very high (100%)	
	a (m)	b (m)	a (m)	b (m)	a (m)	b (m)	a (m)	b (m)
2.5	8	6	10	7	11	8	15	10
4	9	7	11	8	14	9	18	10

Created: 31/03/2014 La legrand

10. CARE

Keep the lens clean.

Clean the surface with a cloth.

Do not use: acetone, tar-removing cleaning agents or trichloroethylene. Resistant to the following products: - Hexane (En 60669-1)

- Methylated spirit
- Soapy water
- Diluted ammonia
- Bleach diluted to 10%
- Window-cleaning products

Attention:

Always test before using other special cleaning products.

12. STANDARDS

Directive: CE

Installation standard: NFC 15-100

Product standards: IEC 60669-2-1

Environmental standards:

- European Directive 2002/96/EC:

WEEE (Waste Electrical and Electronic Equipment).

IGH (high-rise buildings)

- European Directive 2002/95/EC: RoHS (Restriction of Hazardous Substances).

- Regulations: ERP (public buildings) ERT (workplace buildings)

Note:

All technical information is available at

11. TROUBLESHOOTING

PROBLEM	CAUSES	SOLUTIONS
Lighting stays on when there is no-one present	Some sources of interference, such as air	1- Reduce the sensitivity level
	currents, vibrations and radiators, can cause unintended operation	2- If the interference continues: using the configuration tool, go into the Detection system parameters, select Maintain and then choose PIR
		3- If the interference still continues, move the sensor away from sources of interference
Lighting does not switch off during the day	Regulation function not active	Activate the regulation function
when there is an adequate level of natural light	Light level threshold set too high	Reduce the light level threshold
	Light contribution is too high	Check that the sensor is positioned correctly in relation to the window
		Decrease the power of the luminaires
Lighting switches off when there are people	Time delay too short	Increase the time delay
present and the natural light level is not	Detection sensitivity too low	For work areas, choose between
adequate (darkness)	Light level threshold too low	10 and 1 (10 minutes recommended)
		Increase the sensitivity
		Move the sensor closer to the work area
		Increase the threshold

Created: 31/03/2014 **L7 legrand**

Technical data sheet: S000081482EN_2 Updated: 06/09/2022