## L<sup>1</sup> legrand<sup>®</sup>

87045 LIMOGES Cedex Telephone : (+33) 05 55 06 87 87 - Fax : (+33) 05 55 06 88 88

## Keor SPE Tower 750

3 110 60



## **1. GENERAL FEATURES**

The Legrand UPS Keor SPE Tower 750 model is an uninterruptible power source with interactive line technology and sinusoidal output. It delivers a rated power of 750VA – 600W, is managed by a microprocessor, is equipped with integrated self-diagnostics and works on cold-start.

Keor SPE Tower 750 is internally equipped with valve-regulator, hermetically sealed, lead accumulator batteries to guarantee a minimum uptime of 4 minutes at 80% of the load. The batteries can be easily replaced thanks to a specific door located on the front of the UPS.

The presence of an electronic stabilizer (AVR) inside the UPS provides the connected loads with effective protection against any interference in the electrical mains.

This UPS has 2 x (3 x IEC 320-C13) output sockets and 1-group can be programmable.

Keor SPE Tower 750 can be connected to a PC through the SNMP, USB and Serial RS232 port allowing you to monitor its operation, thanks to the free software, and carry out an emergency shutdown of Windows and Linux operating systems.

Through the 5-button control panel, the LCD screen and 3 status LED Bar:

- · GREEN: Everything is OK on UPS. Load is protected.
- YELLOW: The load is supplied by UPS, but an alarm is active, control is required.
- RED: The load is not supplied by UPS. Emergency exists.

LCD display:

- Operation Mode
- Measurements
  - a) Input & Output Voltage-Frequency
  - b) Active & Apparent Power
  - c) Load Percentage
  - d) Battery Voltage
  - e) Battery Percentage
  - f) Back-up time
  - g) Environment Temperature
- Alarms & Errors

The Keor SPE Tower 750 Static Uninterruptible Power Supply bears the CE marking, pursuant to Directives 2014/35 e 2014/30, and is designed and built in compliance with the following standards:

- EN 62040-1 "General and safety requirements for UPSs used in areas that are accessible to the operator"
- EN 62040-2 "Electromagnetic Compatibility requirements (EMC)"
- EN 62040-3 "Performance and test method requirements".

\*This value is based on data collected from a technological channel operating on an industrial basis. It does not prevalidate the effective use of this channel for end-of-life of this product.

TABLE OF	Page

- 1. General features.....1
- 2. Technical features .....1

## 2. TECHNICAL FEATURES

General Features			
Nominal power (VA)	750		
Active power (W)	600		
Technology	Line-interactive VI		
Waveform	Sinusoidal		
Input			
Input voltage	input@AC mode; 1.18*Vin@AVR boost; 0.85*Vin@AVR buck; 230Vac±10%@Battery mode		
Input frequency	47-63Hz (50/60Hz auto-sensing)		
Input Voltage Range	Nominal: 230 / Range: 175 - 288 @ full load		
Input Connection	10A IEC 320-C14		
Output			
Output voltage	230, adjustable to 200/208(output capacity derating to 90%)/220/230/240		
Output frequency (nominal)	50 or 60Hz +/- 0,5 %		
THD Output voltage	< 3% with linear load		
Outlets	2 x (3 x IEC 320-C13) (1-group programmable)		
Batteries			
Number of batteries	2pcs VRLA (Front-access, hot swappable)		
Battery series Type/Voltage	12V, 7Ah		
Charging Time (0-90%)	6-8 hours		
Communication and Management			
Display and Signals	Four buttons and four LEDs to monitor the status of the UPS in real time		
Remote Management	SNMP (independent) and		
500	RS232/USB (use same channel)		
EPO	EPO (adjustable as NC/NO and as Remote ON/OFF via LCD		
Dru Content (NO)	2 pcs: Relay 1: Input failure Relay 2: Battery low		
Dry Contact (NO)			
Protections	Overloads, short-circuit, back-feed,overtemperature		
,	Overloads, short-circuit, back-feed,overtemperature		
Protections	Overloads, short-circuit, back-feed,overtemperature		

Environmental Conditions			
Operating temperature (°C)	0 ÷ 40°C		
Relative humidity (%)	0÷95 % non-condensing		
Noise level at 1 m (dBA)	< 45		
Estimated content of circular economy derived materials	≈41%		
Recyclability rate calculated using the method described in technical report IEC/TR 62635*	≈78%		
Certifications			
Standards	EN62040-1, EN62040-2, EN62040-3		