


6 ports Gigabit PoE+ switch with 1 uplink port and 1 SFP fiber port



1. USE

6-port Gigabit PoE+ switch (with SFP optical port) for shelf or wall mounting.

It is the ideal solution for small business facilities or residential for powering Wi-Fi access points, cameras security, VoIP phones and other devices powered via PoE or non-PoE.

It offers a bandwidth of 12 Gbit/s on 4 Gigabit 802.3af/at PoE+ ports and a budget of 65 W (the maximum power per port is 30 W)

2. DIMENSIONS (mm)

Description	Width	Depth	Height
6 ports Gigabit PoE switch with 1 uplink port and 1 SFP fiber port	210	138	44.5

3. FEATURES

- 6 Gigabit ports
- 4 Gigabit & 802.3af/at PoE/PoE+ ports
- 1 uplink SFP port
- 1 uplink Gigabit Ethernet port
- PoE alimentation budget of 65 W
- Simple management of devices powered via PoE+
- Green LED on front panel, for ethernet link indication
- Silent operation without fan
- Can be mounted on shelf (rubber feet provided) or wall (plugs and screws provided)

Technical data sheet: S000114485EN/00 Updated: Created: 15/01/2021

Cat. No(s): 0 334 93

4. TECHNICAL CHARACTERISTICS

1. IEEE802.3 10 BASE-T Ethernet 2. IEEE802.3u 100 BASE-TX Fast Ethernet 3. IEEE802.3ab 1000 BASE-T GIGABIT Ethernet 4. ANSI/IEEE 802.3 NWAY Auto-negotiation 5. IEEE 802.3af 6. IEEE 802.3at	
1. 4*10M/100M/1000M RJ45 ports support PoE+ injector 2. 1*10M/100M/1000M uplink port 3. 1*GIGABIT SFP port	
1. Connector: RJ-45 2. Supports 10M/100M/1000M Mbit/s rate 3. Supports half-duplex. full duplex, self-negotiation working mode 4. Supports MDI/MDI-X Self-adaptation	
1. 10/100/1000 BASE-TX: 2. Twisted pair, supports maximum transmission distance of 100 meters	
Each port Link Each device Power	
12Gbps	
10Mpbs: 148800pps 100Mpbs: 148800pps 1000Mpbs: 1488000pps	
Storage and Forwarding Mode	
MAC Address Auto-Learning and Auto-Aging Max MAC Address table: 2K	
Single port maximum power: 30W Whole device power: 65W Maximum overload protection power: 60W	
65W AC 100 V ~ 240 V 50/60 HZ	
0°C - 40°C	
Natural cooling	

Cat. No(s): 0 334 93