




1. USE

Cat. 6_A cables with 4 twisted pairs, 100 ohms very high speed, for horizontal floor or backbone distribution. These cables enable the use of protocols supported by Class EA up to 10G Base-T applications. It is characterised up to 500 MHz

802.3 bt PoE++ up to type 4 applications compatible according to installation standards ISO/IEC 14763-2 : 2019 and EN 50174-2 : 2018

2. DESCRIPTION



3. MARKING AND PACKAGING

Marking of Legrand cables

- LEGRAND
- Catalogue number
- Number of pairs
- Gauge
- Type
- Impedance
- Type of sleeve
- Category
- Conformity to standards
- EUROCLASS
- Velocity of propagation
- Traceability
- Measurement (remaining length in metres).

Complementary marking (on label)

- Designation
- Made in....

4. PERFORMANCE AT 500 MHZ (STAND. ISO/IEC 11801)

Reference	6 327 46
Maximum attenuation (dB/100 m)	45,3
Minimum NEXT (dB)	33,8
PS NEXT (dB)	31,8
ACRF (dB / 100 m)	13,8
PS ACRF (dB / 100 m)	10,8
Return Loss (dB)	15,2

5. TECHNICAL AND MECHANICAL FEATURES

Catalogue number	6 327 46
Type	F/UTP
Type of sleeve	PVC
Number of pairs	4
Assembly	Pairs
Diameter over insulation (mm)	1,05±0.05
Average nominal diameter of the cable (mm)	7,0±0.3
Weight of cable (kg/km)	43.5
Min. bending radius when laying (mm)	56
AWG gauge*	24

* According to UL 444 ed.3 table 4

6. ELECTRICAL FEATURES AT 20°C

Catalogue number	6 327 46
Type	F/UTP
Maximum linear resistance (ohm/km)	85 *
DC dielectric strength	1 KV / 1 min *
Minimum insulation resistance (Mohm.km)	5000
Nominal Velocity of Propagation (NVP)	≥65 %
Characteristic impedance at 100 MHz	100 ±5Ω

* According to standard IEC 61156-5

7. ORDERING INFORMATION

Catalogue number	6 327 46
Type	F/UTP
Colour	Yellow sun RAL 1037
Pack (m)	500
Packaging	Reel

8. ENVIRONMENTAL FEATURES

Transport and storage temperature: -20 at + 60 °C
Storage temperature before installation: 10°C during 24h (if stock ≤ 5°C)
Usage temperature: - 20 to + 60 °C

Fire rating: EN 50399, IEC 60332-1-2, EN 60332-1-2

Smoke density : IEC 61034-2, EN 61034-2

Toxicity of fire effluent : IEC 60754-2, EN 60754-2

EUROCLASS EN 13501-6 = Classe Eca

9. STANDARDS AND APPROVALS

Cat 6A, 500 MHz

Electrical performances and characteristics :

ISO/IEC 11801 series : International standard for generic cabling for customer premises

EN 50173 series : European standard for generic cabling for customer premises

IEC 61156 : International standard for twisted pair cable specifications

IEEE 802.3af , IEEE 802.3at , IEEE 802.3bt : "Power over Ethernet", Types 1 to 4, up to 90W