


### 1. USE

Cables with 4 twisted pairs, 100 ohms for high-speed data networks. 802.3 bt PoE++ up to type 4 applications compatible according to installation standards ISO/IEC 14763-2 : 2019 and EN 50174-2 : 2018

### 2. DESCRIPTION

8 x conductors with PE insulation  
 4 pairs with individual aluminium/polyester tape screens



### 3. MARKING AND PACKAGING

Marking of Legrand cables

- LEGRAND
- Catalogue number
- Number of pairs
- Gauge
- Type
- Impedance
- Type of sleeve
- Category
- Conformity to standards
- EUROCLASS
- Velocity of propagation
- Traceability
- Measurement (remaining length in meters).

Complementary marking (on label)

- Designation
- Made in....

### 4. PERFORMANCE

The Cable has a positive PS ACR-F, representing the bandwidth, up to 1200Mhz


#### ■ 4.1 Performance at 1000MHz according to ISO/IEC 11801

Maximum attenuation (dB/100 m):	61,9
Minimum NEXT (dB):	60,4
Minimum PS-NEXT (dB) :	57,4
Minimum ACR-F (dB / 100 m) :	35,3
Minimum PS ACR-F (dB / 100 m) :	32,4
Minimum Return Loss (dB) :	15,1

#### ■ 4.2 Performance of the cable at 1200MHz

Maximum attenuation (dB/100 m):	63.4
Minimum NEXT (dB):	81.0
Minimum PS-NEXT (dB) :	78.0
Minimum ACR-F (dB / 100 m) :	52.0
Minimum PS ACR-F (dB / 100 m) :	39.0
Minimum Return Loss (dB) :	17.0

#### ■ 4.3 Graph of PS ACR-F of the cable vs ISO/IEC 11801



### 5. TECHNICAL AND MECHANICAL FEATURES

Catalogue number	0 328 62
Type	S/FTP
Type of sleeve	LSZH
Number of pairs	4
Assembly	Pairs
Diameter over insulation (mm)	1,4±0.15
Cable diameter (mm)	7,9 ± 0,8
Weight of cable (kg/km)	71
Min. bending radius when laying (mm)	63
AWG gauge*	23

\* According to UL 444 ed.3 table 4

**6. ELECTRICAL FEATURES AT 20°C**

Catalogue number	0 328 62
Type	S/FTP
Maximum linear resistance (ohm/km)	73
DC dielectric strength	1 KV / 1 min *
Minimum insulation resistance (Mohm.km)	5000
Minimum propagation speed	>76 %
Characteristic impedance at 100 MHz	100 ±5Ω

\* According to standard IEC 61156-5

**7. ORDERING INFORMATION**

Catalogue number	0 328 62
Type	S/FTP
Colour	Yellow RAL 1018
Pack (m)	1000
Packaging	Reel

**8. ENVIRONMENTAL FEATURES**

Transport temperature: 0 at + 50 °C

Storage temperature before use: 10°C during 24h (if stock ≤ 5°C )

Usage temperature: - 20 to + 60 °C

Fire rating:EN 50399

IEC 60332-1-2, EN 60332-1-2

Smoke density : IEC 61034-2, EN 61034-2

Toxicity of fire effluent : IEC 60754-2, EN 60754-2

Segregation classification "d" according to ISO/IEC 14763-2

EUROCLASS EN 13501-6 = Class B2ca s1a, d1, a1

Also compliant with Cca, Dca and Eca

**9. STANDARDS AND APPROVALS**

Cat 7A, 1000 MHz

Electrical performances and characteristics :

ISO/IEC 11801 series : International standard for generic cabling for customer premises

EN 50173 series : European standard for generic cabling for customer premises

IEC 61156 : International standard for twisted pair cable specifications

IEEE 802.3af , IEEE 802.3at , IEEE 802.3bt : "Power over Ethernet", Types 1 to 4, up to 90W