

#### Description

Video entrance panel with 10" touch display and badge reader for access control functions. From the touch display, it is possible to make calls to the apartments and the guard station and enter the access code to release the lock. Configuration of different calling modes:

- Apartment code (Area Building Riser Floor Apartment)
- Numeric or alphanumeric codes for residents
- Address book with contact list

Enter the settings menu with a specific code for maintenance and for managing the settings (e.g. backlight brightness, ring volume, speaker volume, touch volume, screensaver time). Possibility to upload customized screensavers and advertisements using the configuration software. The entrance panel can be PoE (power over Ethernet) powered, or directly powered using power supply 375005. Flush mounted installation using the dedicated box 375007.

#### **Related items**

375007 Metal box for flush-mounting installation

### **Technical data**

Voltage: 24 Vdc Maximum consumption: 0.65 A

C NC NO contact output: 125 Vac/0.5A, 30Vdc/2A

Max. cable section for clamps: 0.8 mm<sup>2</sup>

Operating temperature: (-40) - (+70) °C

IP degree of protection: 54

IK degree of protection: 07


Camera resolution: 1080 p

Camera viewing field angle: H= 80°; V= 53°

Badge reader Frequency: 13.56 MHz

Badge reader transmission power: < 42 dBuA/m @ 10m

### **Dimensional data**



C

58 mm

#### Front view



### Legend

- 1. Microphone
- 2. LED for the shooting field lighting
- 3. Camera
- 4. Light sensor
- 5. Display 10" (touch screen)
- 6. Home Page
- 7. Badge reader for door lock opening
- 8. Loudspeaker
- 9. Locking screws



195 mm


В

430 mm

D


12 mm

Rear view



### Legend


- 1. Tamper switch
- 2. SD card
- 3. Connection clamp
- 4. Not used
- 5. Not used
- 6. Mounting bracket
- 7. USB Connector (not used)
- 8. RJ45 Connector (\*)
- 9. Reset setting password and local access code
- (\*) This device does not support standard POE power supplies, but only POE power supplies identified with item no. 375002. Connect the cat5/5e/6 FTP or cat5/5e/6 UTP cable with ferrite supplied to the connector. The wrong wiring of the Ethernet cable connecting the device to the Poe Switch 375002 could damage the device itself. The RJ45 cable must be at least 200 mm long



Connection clamps			
LOCK+		electric door lock connection and control	
LOCK-		(12V - 4A impulsive on 30 0hm maximum)	
SENSE		door status signal input (dry contact)	
GND		system common ground terminal for third party connection	
OPEN		third party access control signal input for door lock opening (+12Vdc pulse)	
GND		access control devices power supply	
+12V			
Door OPEN – GND		local door lock release pushbutton connection	
FIRE Linkage –		local door lock release pushbutton connection for firealarm	
GND		system	
NO			
C		interlocked contact	
NC			
DC24V		additional power supply clamps (not polarized)	
RS485A	ift Control	terminal A	
RS485B		terminal B	
GND	Lift (	system common ground terminal for RS485 connection	

### Configuration

To use the device, it is necessary to configure it and create the Community structure using the IP DES System software, following the steps below:




For further information, please refer to the IP DES System Software Manual and Small video entrance panel manual, available for download from www.homesystems-legrandgroup.com website



Wiring diagrams				
CABLES LEGEND	LAN PoE BTicino ———	LAN Ethernet ———	Copper cables ———	2 x Copper cables ———

It is possible to use two different types of connection according to installation situation:




**Attention:** This device does not support standard POE power supplies, but only POE power supplies identified with 375002. Connect the cat5/5e/6 FTP or cat5/5e/6 UTP cable with ferrite supplied to the connector.

**Attention:** Do not directly connect PoE ports to an unsuitable network interface, such as a device powered by a different voltage. Connect the UP LINK port to a suitable port, never to a PoE port. **Note:** To connect the devices it is possible to use both types of wiring (diagram A or diagram B) or even mixed ones.

**Note:** Maximum length of every LAN permanent link line = 90 m.






Attention: do not directly connect PoE ports to an unsuitable network interface, such as a device powered by a different voltage. Connect the UP LINK port to a suitable port, never to a PoE port. Note: to connect the devices it is possible to use both types of wiring (diagram A or diagram B) or even mixed ones.



ST-00001217-EN 27/09/2023




Attention: do not directly connect PoE ports to an unsuitable network interface, such as a device powered by a different voltage. Connect the UP LINK port to a suitable port, never to a PoE port. Note: to connect the devices it is possible to use both types of wiring (diagram A or diagram B) or even mixed ones.



ST-00001217-EN 27/09/2023


Lift control 1 - Lift control, 1 riser, 1 entrance panel

CABLES LEGEND LAN POE BTicino LAN Ethernet Copper cables 2 x Copper cables 2 x Copper cables —




Attention: do not directly connect PoE ports to an unsuitable network interface, such as a device powered by a different voltage. Connect the UP LINK port to a suitable port, never to a PoE port. Note: to connect the devices it is possible to use both types of wiring (diagram A or diagram B) or even mixed ones.





Attention: do not directly connect PoE ports to an unsuitable network interface, such as a device powered by a different voltage. Connect the UP LINK port to a suitable port, never to a PoE port. Note: to connect the devices it is possible to use both types of wiring (diagram A or diagram B) or even mixed ones.






Attention: do not directly connect PoE ports to an unsuitable network interface, such as a device powered by a different voltage. Connect the UP LINK port to a suitable port, never to a PoE port. Note: to connect the devices it is possible to use both types of wiring (diagram A or diagram B) or even mixed ones.



Available functions				
CABLES LEGEND	LAN PoE BTicino ———	LAN Ethernet ———	Copper cables ———	2 x Copper cables ———



Attention: do not directly connect PoE ports to an unsuitable network interface, such as a device powered by a different voltage. Connect the UP LINK port to a suitable port, never to a PoE port. **Note:** to connect the devices it is possible to use both types of wiring (diagram A or diagram B) or even mixed ones.



27/09/2023

#### **Main functions**

From the Home Page of the device, it is possible to access the main functions, as described below:



### Call an IU Function

In this section it is possible to manage the calls to an IU.

Depending on how the community has been configured using the DES Server software, calls can be made in different ways:

- Call using the system address
- Call using the Alias (alphanumeric code)
- Call using the Phonebook

When the IU does not answer a message can be recorded.

#### Call a GS Function

This function allows to call the reference guard station.

#### **Access Function**

It is possible to access the building in different ways:

- by entering a code, using the Access using Code function on the Home Page  $\,$
- using a configured badge or card.

#### **Answering machine Function**

Using this function, it is possible to leave a photo with own audio message if the IU does not answer after 30 seconds. This function must be active.

### Messages and advertising Function

This function displays advertising messages or images sent to entrance panels through the DES Server Software.

