


Rear terminals for DMX³ 2500, 4000 and 6300




Dimensions **see e-catalogue**

Pack	Cat.Nos		Rear terminals
1	3P 0 288 84	4P 0 288 85	For DMX³ frame 2500 fixed version For flat connection with bars To be fixed onto horizontal rear terminals of the circuit breaker
1	0 288 82	0 288 83	For vertical connection with bars Those terminals are used in order to transform a flat connection into a vertical one To be fixed onto Cat.Nos 0 288 84/85 according to the number of poles
1	0 288 96	0 288 97	For DMX³ frame 2500 draw-out version For vertical or horizontal connection with bars To be fixed onto plate rear terminals of the circuit breaker
1	0 288 92	0 288 93	For DMX³ frame 4000 and 6300 fixed version For flat connection with bars To be fixed onto horizontal rear terminals of the circuit breaker 2 sets are required for frame 6300
1	0 288 94	0 288 95	For DMX³ frame 4000 and 6300 fixed or draw-out version On DMX ³ fixed version: - For vertical connection with bars - To be fixed onto Cat.Nos 0 288 92/93 according to the number of poles On DMX ³ draw-out version: - For vertical or horizontal connection with bars - To be fixed directly onto plate rear terminals of the circuit breaker 2 sets are required for frame 6300

Pack	Cat.Nos		Spreaders for DMX ³ frame 2500 fixed version
1	3P 0 288 86	4P 0 288 87	To be fixed onto horizontal rear terminals of the circuit breaker
1	0 288 88	0 288 89	For flat connection with bars
1	0 288 90	0 288 91	For vertical connection with bars For horizontal connection with bars

Pack	Cat.Nos		Insulation shields
1	3P 0 288 98	4P 0 288 99	For fixed version Insulation shields for DMX ³ /DMX ³ -I frames 2500 / 4000 / 6300
1	0 288 18	0 288 19	For draw-out version Insulation shields for DMX ³ /DMX ³ -I frames 2500 / 4000 / 6300

Equipment for DMX³ 2500, 4000 and 6300 transfer switches



Technical characteristics **see e-catalogue**

Pack	Cat.Nos	Equipment for transfer switches
1	0 288 64	The mechanical interlock is set up using cables and can interlock 2 or 3 devices, which may be different type in a vertical or horizontal configuration The interlock unit is mounted on the right-hand side of the device Cable interlock to be ordered separately (cable length to be specified according to every configuration - see below) Interlock for DMX ³ frame 2500
1	0 288 65	Interlock for DMX ³ frame 4000
1	0 288 66	Interlock for DMX ³ frame 6300
Cable interlock		
Length		
1	0 289 17	1000 mm
1	0 289 18	1500 mm
1	0 289 20	2600 mm
1	0 289 21	3000 mm
1	0 289 22	3600 mm
1	0 289 23	4000 mm
1	0 289 24	4600 mm
1	0 289 25	5600 mm

CTX³ 3-pole contactors
p. 190

Power supervision system
p. 105