

Equipment for DMX³ 1600 transfer switches



0 289 20

Pack	Cat.Nos	Equipment for transfer switches
1	0 281 90	Interlock for DMX ³ frame 1600
Cable interlock		
Length		
1	0 289 17	1000 mm
1	0 289 18	1500 mm
1	0 289 20	2600 mm
1	0 289 21	3000 mm
1	0 289 22	3600 mm
1	0 289 23	4000 mm
1	0 289 24	4600 mm
1	0 289 25	5600 mm

The mechanical interlock is set up using cables and can interlock devices, which may be different type in a vertical or horizontal configuration. The interlock unit is mounted on the right-hand side of the device.

Cable interlock to be ordered separately (cable length to be specified according to every configuration - see below).

Interlock for DMX³ frame 1600


Cable interlock

Length

1	0 289 17	1000 mm
1	0 289 18	1500 mm
1	0 289 20	2600 mm
1	0 289 21	3000 mm
1	0 289 22	3600 mm
1	0 289 23	4000 mm
1	0 289 24	4600 mm
1	0 289 25	5600 mm

Equipment for DMX³ 1600 transfer switches - installation principle

Choice of cable interlock



Calculation of cable length:

$$L1 = 600 + H$$

$$L2 = 950 + V$$

Installation principle

For XL³ 4000 - 36 modules

2 DMX³ / DMX³-I can be installed side by side on the same fixing plate.

