


Céliane™ with Netatmo Connected Wake up/Sleep wireless control

Cat. Nos: 0 648 84A/85A/86A



1. USE


Used to control wake up/sleep scenes involving lights, roller shutters and connected sockets.


- Fixes directly on the wall or screws onto a flush-mounting box. Multi-gang versions can be combined with other wiring accessories.
- Fits on a piece of furniture (movable).

2. RANGE

Description	White	Titanium	Graphite
Wake up/Sleep wireless control, with battery. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings supplied. To be equipped with cover-plate.	0 648 84A	0 648 85A	0 648 86A


3. DIMENSIONS





Α	В	С
74	74	13

4. OPERATION




Wake up scenario when pressed at the top: By default, switches on the connected sockets Can be customised with the Home + Control app

LED indicator:

- useful during installation
- when pressed, burst flashes red if the battery power is low

Sleep scenario when pressed at the bottom: By default, switches off all the lights in the installation Can be customised with the Home + Control app



RESET button used to return to factory settings

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02 Protection against solid bodies/liquids:

- IP 20 without plate and rocker plate
- IP 40 for assembled product

■ 5.2 Material characteristics

Mechanism with grid: Fibreglass-reinforced (10%) PC

Colour	White RAL 9003	Titanium	Graphite
Rocker plate	ABS	Painted ABS	Painted ABS

Halogen-free

UV resistant

Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied) Battery life: 8 years for 10 activations a day

ZigBee radio technology

frequency: 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

■ 5.4 Climate characteristics

Usage temperature: $+ 5^{\circ}\text{C}$ to $+ 45^{\circ}\text{C}$ Storage temperature: 0°C to $+ 45^{\circ}\text{C}$

Céliane™ with Netatmo Connected Wake up/Sleep wireless control

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.



Take care to recycle the battery appropriately

7. ACCESSORIES

0 648 71: Repositionable adhesive for wireless control (supplied)

Replacement rocker plate: 0 648 11: White

0 648 21: Titanium 0 648 31: Graphite

8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (0 648 84A/85A/86A) complies with directive 2014/53/EU. The full text of the EU declaration of conformity is available on the following website: www.legrandoc.com

Created: 12/01/2018 La legrand