


Arteor™ with Netatmo Wireless colour ambiance switch



1. USE

Wireless switch to control multicolor smart lighting.

Controls any king of Zigbee 3.0 certified bulbs and lighting (such as Ledvance, Smart + Zigbee, Philips HUE and many others).

Can be used as a two-way switch or to control a lighting group.


- Fixes directly on the wall or screws onto a flush-mounting box.
- Fits on a piece of furniture (movable).

Can control up to 20 connected zigbee 3.0 lights.

2. RANGE

Description	White	Magnesium	Champagne	Soft Alu
Wireless switch for multicolor ambiance - 2 modules 3 ambiances (I - II - III) to select in Home + Control App. Supplied with secable support frame, rocker plate and a battery. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings (supplied).	5 744 34	5 744 35	5 744 36	5 744 37


3. DIMENSIONS (mm)






Α	В	B'	C
82	116.5	82	12

4. OPERATION



Cat. Nos: 5 744 34/35/36/37



Arteor™ with Netatmo Wireless colour ambiance switch

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against impacts: IK 02

Protection against solid bodies and/or liquids: IP 20

IP 40 mounted product

■ 5.2 Material characteristics

Rocker plate: ABS

Mechanism casing with grid: Fibreglass-reinforced (10%) PC

Halogen-free UV resistant

Self-extinguishing: 650°C/30 s

■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied) Battery life: 8 years for 10 activations a day

Frequency bands: 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

■ 5.4 Climate characteristics

Usage temperature: $+5^{\circ}$ C to $+45^{\circ}$ C Storage temperature: 0° C to $+45^{\circ}$ C

6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products:

Hexane, methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.



Take care to recycle the battery appropriately.

7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (5 744 34/35/36/37) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: ${\bf www.legrandoc.com}$

Compliant with installation and manufacturing standards. See e.catalogue.

Cat. Nos: 5 744 34/35/36/37